


盘头螺钉，米字槽



盘头螺钉，Pozidrive。

功能

盘头螺钉，米字头

Pozidriv has a set of 45° radial indentations from the main cross recess leading to 4 additional contact points and greater stabilization to provide a greater contact surface. As a result, it decrease cam-out and wear, which allows greater torque to be applied.

材料: 钢
产品类型: 螺钉



技术参数

Table 1/2

物料号	直径	长度	完成	包装数量	螺纹尺寸	产品系列
21100-788		12m m	镀锌	100	M5	EuropacPRO
21120-150	5mm	10m m	镀锌	100	M5	
21101-222		16m m	镀镍	100	M2.5	框架式插入单元
21101-221		12m m	镀镍	100	M2.5	框架式插入单元
21101-220		10m m	镀镍	100	M2.5	框架式插入单元
21101-219		6mm	镀镍	100	M2.5	框架式插入单元
21102-024	3mm	6mm	镀锌	100	M3	
21100-021	6mm	16m m	镀锌	50	M6	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO

物料号	直径	长度	完成	包装数量	螺纹尺寸	产品系列
21100-022	6mm	16mm	镀锌	100	M6	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO
21101-314		5mm	镀镍	100	M2.5	
21100-650	6mm	16mm	Zinc Plated, Black	100	M6	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO
21101-069		8mm	镀镍	100	M2.5	框架式插入单元
21120-202	6mm	16mm	镀锌	50	M6	
21120-203	6mm	16mm	镀锌	100	M6	

Table 2/2

物料号	类型	搭配	螺纹长度	螺纹类型	认证
21100-788	盘头螺钉	插箱	12mm		RoHS
21120-150	编码块	机柜	10mm		RoHS
21101-222	盘头螺钉	背板, 测试适配器	16mm		RoHS
21101-221	盘头螺钉	背板, 测试适配器	12mm		RoHS
21101-220	盘头螺钉	背板, 测试适配器	10mm		RoHS
21101-219	盘头螺钉	背板, 测试适配器	6mm		RoHS
21102-024	盘头螺钉		6mm	公制	RoHS
21100-021	盘头螺钉	前面板, Eurorack, Novastar, Varistar, Varistar CP	16mm		RoHS
21100-022	盘头螺钉	前面板, Eurorack, Novastar, Varistar, Varistar CP	16mm		RoHS
21101-314	盘头螺钉	背板, 测试适配器	5mm		RoHS
21100-650	盘头螺钉	前面板, Eurorack, Novastar, Varistar, Varistar CP	16mm		RoHS
21101-069	盘头螺钉	背板, 测试适配器	8mm		RoHS
21120-202	盘头螺钉	前面板, Eurorack, Novastar, Varistar, Varistar CP	16mm		
21120-203	盘头螺钉	前面板, Eurorack, Novastar, Varistar, Varistar CP	16mm		

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff

