

PMC 夹层卡前面板, 非屏蔽型



夹层前面板安装在 PMC

前面板开孔中。提供不同处理方式的版本。

功能

夹层前面板安装在带 PMC 开孔的前面板中

EMC 屏蔽, 带导电 O 型圈



技术参数

Table 1/3

物料号	类型	附件类型	安装	EMC 屏蔽	垫片类型	材料
20835-899	夹层前面板	前面板	卡扣嵌入式	无 (可改装)	O 形环 EMC	铝
20835-896	不带把手的前面板		正面螺钉安装	无 (可改装)		锌
20835-929	不带把手的前面板		正面螺钉安装	无 (可改装)		锌
20835-931	不带把手的前面板		正面螺钉安装	无 (可改装)		锌

Table 2/3

物料号	正面表面处理	反面表面处理	边缘处理	高度	宽度	符合
20835-899	阳极氧化	导电	是	74mm	12.7mm	PMC 夹层板, IEEE P1386
20835-896	阳极氧化	阳极氧化	否	74mm	12.7mm	PMC 夹层板, IEEE P1386
20835-929	镀铬	镀铬	是	74mm	12.7mm	PMC 夹层板, IEEE P1386
20835-931	阳极氧化	导电	否	74mm	12.7mm	PMC 夹层板, IEEE P1386

Table 3/3			
物料号	深度	包装数量	完成
20835-899	2.5mm	10	阳极氧化
20835-896		10	
20835-929		10	
20835-931		10	

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

