

Varistar CP Cabeling Rack



符合高静态负载要求的焊接钢框架。适合高电缆密度和 19" 集成。

功能

预配置, 立即可用型机柜

静态承载重能力高达 1600 千克

防护等级 IP 20

可安装不同类型的网络设备

集成垂直和水平电缆管理部件

可轻松集成到通道密封系统中

框架材料: 钢
材料: 钢
产品类型: 机架

技术参数

Table 1/2

物料号	机架高度	覆层材料	框架颜色	高度	框架颜色代码	覆层颜色
10630-027	42U	钢	暗灰色	2000mm	RAL 7021	暗灰色
10630-028	42U	钢	暗灰色	2000mm	RAL 7021	暗灰色

Table 2/2

物料号	宽度	深度	静态负载	覆层颜色代码	包装数量	动态荷载	完成
10630-027	800mm	1200mm	1600kg	RAL 7021	1	1000kgf	粉末涂层
10630-028	800mm	1200mm	1600kg	RAL 7021	1	1000kgf	粉末涂层

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书, 或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告, 可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff

