

Stainless Steel Plain Door, DNSS



This door replaces the rear panel in a floor standing enclosure to allow for rear access of equipment installed in the front, or for using back to back mounting plates to increase the enclosure's mounting space.

FEATURES

Description: Standard door equipped with double-bit 3 mm lock system and door frame. Door accessory kit DNPKS (hinges, rod catches) to be ordered separately. Allows all the options of the locking programme and 180° hinges. Compatible with combinable and compact stainless steel enclosure ranges.

Material: 2 mm AISI 304 stainless steel plate / AISI 316L (on request).

Maximum load: 800 N.

Finish: 400 pre-grained stainless steel.

Pack quantity: 1 piece.

Mounting requirements: Use hinge kit DNPKS if no door was fitted previously.

Thickness: 2mm
Finish: Brushed
Material: Stainless Steel 304

SPECIFICATIONS

Table 1/2

Catalog Number	Height	Width	Depth	Door Type	Product Family	Enclosure Material
DNSS1606	1600mm	600mm	17mm	Single Door	Free-Standing	Mild Steel
DNSS2012R	2000mm	600mm	17mm	Right Door	Free-Standing	Mild Steel

Catalog Number	Height	Width	Depth	Door Type	Product Family	Enclosure Material
DNSS1612L	1600mm	600mm	17mm	Left Door	Free-Standing	Mild Steel
DNSS1408	1400mm	800mm	17mm	Single Door	Free-Standing	Mild Steel
DNSS2008	2000mm	800mm	17mm	Single Door	Free-Standing	Mild Steel
DNSS1812L	1800mm	600mm	17mm	Left Door	Free-Standing	Mild Steel
DNSS1810L	1800mm	500mm	17mm	Left Door	Free-Standing	Mild Steel
DNSS2006	2000mm	600mm	17mm	Single Door	Free-Standing	Mild Steel
DNSS1212R	1200mm	600mm	17mm	Right Door	Free-Standing	Mild Steel
DNSS1610	1600mm	1000mm	17mm	Single Door	Free-Standing	Mild Steel
DNSS2016L	2000mm	800mm	17mm	Left Door	Free-Standing	Mild Steel
DNSS1612R	1600mm	600mm	17mm	Right Door	Free-Standing	Mild Steel
DNSS1810	1800mm	1000mm	17mm	Single Door	Free-Standing	Mild Steel
DNSS1808	1800mm	800mm	17mm	Single Door	Free-Standing	Mild Steel
DNSS1816L	1800mm	800mm	17mm	Left Door	Free-Standing	Mild Steel
DNSS2012L	2000mm	600mm	17mm	Left Door	Free-Standing	Mild Steel
DNSS1608	1600mm	800mm	17mm	Single Door	Free-Standing	Mild Steel
DNSS1810R	1800mm	500mm	17mm	Right Door	Free-Standing	Mild Steel
DNSS1812R	1800mm	600mm	17mm	Right Door	Free-Standing	Mild Steel
DNSS1806	1800mm	600mm	17mm	Single Door	Free-Standing	Mild Steel

Table 2/2

Catalog Number	Height	Width	Depth	Door Type	Product Family	Enclosure Material
DNSS2016R	2000mm	800mm	17mm	Right Door	Free-Standing	Mild Steel
DNSS1816R	1800mm	800mm	17mm	Right Door	Free-Standing	Mild Steel
DNSS1212L	1200mm	600mm	17mm	Left Door	Free-Standing	Mild Steel
DNSS2010	2000mm	1000mm	17mm	Single Door	Free-Standing	Mild Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE