


# Rooftop Pyramid Equipment Support Kit, 4 Post Base, 1257 mm



## KATALOGOVÉ ČÍSLO

**PEK4B**

## VLASTNOSTI

Kit includes post-base assemblies, frame and equipment-support clamps

Assembles and adjusts to size and height in minutes by one person with one tool

Innovative crossbar and equipment-support clamps enable quick assembly

Integral foam pad provides gentle interface for all roof types

Hot-dip galvanized and UV stabilized for long lasting performance

Assembled support can be lifted as one unit and easily relocated



## VLASTNOSTI PRODUKTU

Article Number: 360426

Materiál: Ocel; Polypropylene; Polyetylen

Povrchová úprava: Hot-Dip Galvanized

Temperature: -34 to 54.4 °C

Height (H): 305 - 457 mm

Length (L): 1257mm

Post Base (A): 314 mm x 4 pc

Square Tube (B): 1067 mm x 2 pc

Cross Bar Assembly (C): 1232 mm x 2 pc

Width (W): 1588 mm

Surface Area: 0.36m<sup>2</sup>

Unit Weight: 36 kg



Ultimate Static Load (F): 4980N

Static Load Safety Factor: 3:1

## DALŠÍ PODROBNOSTI O PRODUKTU

Static load must be stable and uniformly distributed across frame.

## DIAGRAMS



## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

[nVent.com/ENDDT](http://nVent.com/ENDDT)

