

Wire Basket Tray Center Support



The nVent CADDY Wire Basket Tray Center Support is a simple and efficient way to support wire basket trays from a single threaded rod. The offset center tube helps ensure the tray is centered and secured, enhancing both structural integrity and improving project efficiency. Designed for light-duty cable support projects, installation is easy—simply hold the Center Support parallel to the tray, then turn perpendicular until you hear the Center Support lock into place.

Compatible with varying nVent CADDY Wire Basket Tray sizes, the ceiling support is precision-engineered to handle the weight of the trays with confidence. Its pre-punched design simplifies mounting with standard fasteners. Its compatibility with various finishes—including pre-galvanized, zinc electroplate, and powder coat options—adds aesthetic and functional versatility to any project.

VLASTNOSTI

Use as a central support when hanging with threaded rod

Designed to be used with the nVent CADDY Wire Basket Tray Splice Kit

Supported with 3/8 or 1/2 in threaded rod


Materiál: Ocel
Povrchová úprava: Electrogalvanized



SPECIFIKACE

Katalogové číslo	Barva	Height (H)	Width (W)	Length (L)	Hole Size (HS)	Unit Weight
WBTCTSPRT12		193.55 mm	41.4 mm	292.176mm	15.75 mm	1.225 kg
WBTCTSPRT4		193.55 mm	41.4 mm	105.156mm	15.75 mm	0.7 kg
WBTCTSPRT4BA	Black	193.55 mm	41.4 mm	105.156mm	15.75 mm	0.7 kg
WBTCTSPRT6		193.55 mm	41.4 mm	147.777mm	15.75 mm	0.816 kg
WBTCTSPRT8		193.55 mm	41.4 mm	190.551mm	15.75 mm	0.907 kg

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/GRDDT

