


EuropacPRO Cover Plate for Bolting to Side Panel, SNCF



A cover plate is used for electromagnetic shielding or as mechanical protection. The cover can be screwed onto the side panel. Can be used for railway subracks in accordance with SNCF.

VLASTNOSTI

For variable positioning of horizontal rails e.g. for PCBs with standard formats

Perforation degree 58 %

Suitable for use with all horizontal rails

Materiál:	Hliník
Product Type:	Cover Plate
Produktová řada:	EuropacPRO
Povrchová úprava:	Passivated
Typ:	Perforated
Works With:	Subracks



SPECIFIKACE

Katalogové číslo	Rack Width	Hloubka	Množství v balení	Balení	Torque
21500-037	84HP	235mm	2	Pair	2.1N·m
21500-124	36HP	175mm	2	Pair	2.1N·m
21500-123	36HP	55mm	2	Pair	2.1N·m
21500-122	36HP	235mm	2	Pair	2.1N·m
21500-048	84HP	175mm	2	Pair	2.1N·m
21500-038	84HP	55mm	2	Pair	2.1N·m

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná

instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE