

PMC Mezzanine Front Panel, Untreated, With EMC Shielding



Mezzanine front panel is fitted into PMC front panel cut-outs. Available in different treatments. For O-ring EMC gasket.

VLASTNOSTI

Mezzanine front panel is fitted into PMC front panel cut-outs

EMC shielding with conductive O-ring

EMC Shielding: Yes
Product Type: Front Panel
Typ: Front Panel without Handle



SPECIFIKACE

Table 1/2

Katalogové číslo	Množství v balení	Accessory Type	Mounting	Gasket Type	Front Finish	Rear Finish
20835-598	1	Front panel	Screw-on Front	O-Ring EMC	Anodized	Conductive
20835-889	1	Front panel	Screw-on Front	O-Ring EMC	Anodized	Conductive
20835-890	1		Screw-on Front			
20835-893	10		Screw-on Front		Chrome Plated	Chrome Plated
20835-922	1		Screw-on Front		Chrome Plated	Chrome Plated
20835-923	1		Screw-on Front		Chrome Plated	Chrome Plated
20835-924	10		Screw-on Front		Chrome Plated	Chrome Plated
20835-928	10		Screw-on Front		Anodized	Conductive

Table 2/2

Katalogové číslo	Treated Edges	Complies With	Hloubka	Povrchová úprava	Výška	Materiál	Šířka
20835-598	No	PMC Mezzanine, IEEE P1386	2.5mm	Anodized	74mm	Hliník	12.7mm

Katalogové číslo	Treated Edges	Complies With	Hloubka	Povrchová úprava	Výška	Materiál	Šířka
20835-889	No	PMC Mezzanine, IEEE P1386	2.5mm	Anodized	74mm	Hliník	12.7mm
20835-890	No	PMC Mezzanine, IEEE P1386			74mm	Zinc	12.7mm
20835-893	Yes	PMC Mezzanine, IEEE P1386			74mm	Zinc	12.7mm
20835-922	Yes	PMC Mezzanine, IEEE P1386			74mm	Zinc	12.7mm
20835-923	Yes	PMC Mezzanine, IEEE P1386			74mm	Zinc	12.7mm
20835-924	Yes	PMC Mezzanine, IEEE P1386			74mm	Zinc	12.7mm
20835-928	No	PMC Mezzanine, IEEE P1386			74mm	Zinc	12.7mm

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.