

Quick Release Fastener

1/4 rotary lock with defined stop.

VLASTNOSTI

1/4 rotary lock with defined stop

Identification of locking position due to slot position

Vibration and shake proof

Qty 100 pieces

Works With:	Front Panels
Product Type:	Hardware Kit
Povrchová úprava:	Nickel Plated
Materiál:	Ocel; Zinc Alloy; Thermoplastic



SPECIFIKACE

Katalogové číslo	Barva	Množství v balení	Kód barvy	Hloubka	Výška	Šířka	Fastener Type
21101-850	Jet Black	100	RAL 9005	20.6mm	6mm	7mm	Knurled, Slotted Head
21101-847	Pebble Grey	100	RAL 7032	16.7mm	6mm	7mm	Slotted Head
21101-849	Pebble Grey	100	RAL 7032	20.6mm	6mm	7mm	Knurled, Slotted Head
21101-848	Jet Black	100	RAL 9005	16.7mm	6mm	7mm	Slotted Head

DALŠÍ PODROBNOSTI O PRODUKTU

Quick-release fasteners: mounting without threaded inserts.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE