

Mains Cable



nVent SCHROFF Mains cable provides practical, universal fastening with variable attachment facilities. They are general in nature and fit in to different applications like Fans, cabinet lights, etc., Industrial PC connections, Uninterruptible power supplies, Systems.

VLASTNOSTI

Applications: Fans, cabinet lights, Industrial PC connections, Uninterruptible power supplies and Systems

Product Type: Cable



SPECIFIKACE

Katalogové číslo	Input Connector	Output Connector	Length	Množství v balení	Barva	Connector Type	Materiál
60103-131	SCHUKO / UTE	IEC C13	2500m m	1	Grey	Straight	PVC
60103-137	BS = British Standard	IEC C13	2500m m	1	Black	Straight	PVC
60103-141	US = US Standard	IEC C13	2500m m	1	Black	Straight	PVC
60197-053	IEC C14	IEC C13	2500m m	1	Black	Straight	PVC
60110-361	IEC C14	IEC C13	1000m m	1	Black	Straight	PVC
60704-020	SCHUKO / UTE	IEC C13	2500m m	1	Grey	Angled	PVC
62150-191	SCHUKO / UTE	IEC C13	2500m m	1	Black	Straight	PVC
60110-360	IEC C14	IEC C13	500mm	1	Black	Straight	PVC

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.