

# MTCA.4 Front Panel

AdvancedTCA front panel (stainless steel) for textile gasketing. Shielded filler modules are used to close unused slots.

## VLASTNOSTI

In accordance with MicroTCA.1 and MicroTCA.4 specifications

Shielded filler modules are used to close unused slots

Can be screwed on; is supported on the guide rail

|                         |                 |
|-------------------------|-----------------|
| <b>Produktová řada:</b> | AdvancedMC      |
| <b>Accessory Type:</b>  | Front panel     |
| <b>Typ:</b>             | Front Panel     |
| <b>Product Type:</b>    | Front Panel     |
| <b>Materiál:</b>        | Stainless Steel |
| <b>EMC Shielding:</b>   | Yes             |



## SPECIFIKACE

Table 1/2

| Katalogové číslo | Výška   | Rack Width | Množství v balení | Mounting       | Gasket Type | Front Finish |
|------------------|---------|------------|-------------------|----------------|-------------|--------------|
| 20849-214        | 170mm   | 2HP        | 1                 | Screw-on Front | Textile EMC | Raw          |
| 20849-213        | 95mm    | 2HP        | 1                 | Screw-on Front | Textile EMC | Raw          |
| 21850-102        | 84.68mm |            | 1                 | Screw-on Front | Textile EMC | Raw          |
| 21850-103        | 84.68mm |            | 1                 | Screw-on Front | Textile EMC | Raw          |

Table 2/2

| Katalogové číslo | Rear Finish | Hloubka | Šířka   |
|------------------|-------------|---------|---------|
| 20849-214        | Raw         | 0.6mm   | 8.8mm   |
| 20849-213        | Raw         | 0.6mm   | 8.8mm   |
| 21850-102        | Raw         | 1mm     | 18.96mm |
| 21850-103        | Raw         | 1mm     | 28.98mm |

## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit

selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Naše portfolio silných značek:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**