


4G24 Twist Clip with Stud



FUNKTIONER

Supports electrical fixtures from acoustical T-grid

No tools required for installation

Fast, easy and secure twist-on installation

Designed to reduce scratching of T-grid

Nut sold separately

Materiale: Spring Stål;Stål



SPECIFIKATIONER


Table 1/2

Katalognummer	Artikelnummer	Finish	Farve	Screw Length (L)	Flange Thickness (FT)	T-Grid Size
4G24M11	171680	nVent CADDY Armour	Gray	11mm	1.5 mm	24mm
4G24M11WH	171840	Painted	White	11mm	1.5 mm	24mm
4G24M16	171710	nVent CADDY Armour	Gray	16mm	1.5 mm	24mm
4G24M16WH	171860	Painted	White	16mm	1.5 mm	24mm
4G24M16WHSP25	172290	Painted	White	16mm	1.5 mm	24mm
4G24M25	171730	nVent CADDY Armour	Gray	25mm	1.5 mm	24mm
4G24M25WHSP25	172300	Painted	White	25mm	1.5 mm	24mm

Table 2/2

Katalognummer	Artikelnummer	Screw Diameter (Sc)	Static Load
4G24M11	171680	6	220N
4G24M11WH	171840	6	220N
4G24M16	171710	6	220N
4G24M16WH	171860	6	220N
4G24M16WHSP25	172290	6	220N
4G24M25	171730	6	220N
4G24M25WHSP25	172300	6	220N

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

