

Wire Basket Tray Cover



The nVent CADDY Wire Basket Tray Cover provides dependable top-side protection for high-performance cables installed in continuous pathways. Featuring a tool-free, snap-on design with integrated indents that lock securely over the top tray wires, the Cover installs in seconds—no screwdriver, no additional hardware.

Designed to conform with the nVent CADDY Wire Basket Tray, its steel construction helps safeguard critical systems in demanding environments—such as data centers—while supporting a clean, consistent and fast installation.

FUNKTIONER

Tool-free, snap-on installation locks securely without additional hardware

Solid steel construction helps prevent dust and debris from falling onto cables

Designed to fit over nVent CADDY Wire Basket Tray

SPEKIFIKATIONER

Katalognummer	Materiale	Finish	Farve
COVER12	Stål	Pregalvanized	
COVER12BA	Stål	Pregalvanized	Black
COVER12S4	Stainless Steel 304		
COVER18	Stål	Pregalvanized	
COVER18BA	Stål	Pregalvanized	Black
COVER18S4	Stainless Steel 304		
COVER2	Stål	Pregalvanized	
COVER24	Stål	Pregalvanized	
COVER24BA	Stål	Pregalvanized	Black
COVER2BA	Stål	Pregalvanized	Black
COVER2S4	Stainless Steel 304		
COVER4	Stål	Pregalvanized	
COVER4BA	Stål	Pregalvanized	Black

Katalognummer	Materiale	Finish	Farve
COVER4S4	Stainless Steel 304		
COVER6	Stål	Pregalvanized	
COVER6BA	Stål	Pregalvanized	Black
COVER8	Stål	Pregalvanized	
COVER8BA	Stål	Pregalvanized	Black
COVER8S4	Stainless Steel 304		

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

