

Wire Basket Tray L Bracket



The nVent CADDY Wire Basket Tray L Bracket delivers a clean, space-efficient solution for supporting wire basket trays in data application environments. Unlike multi-tier or ceiling-mounted supports, the L Bracket is optimized for single-plane, wall-mounted runs, making it ideal for installations where floor space is limited or ceiling access is restricted.

Its low-profile design simplifies installation without compromising strength. The bracket's side-load access allows for seamless cable placement, even in retrofit scenarios. At nVent CADDY, we are committed to providing you with innovative product offerings that empower you and solve your problems, not matter how complex.

FUNKTIONER

Easy-to-use quick connect feature

Designed to be used with the nVent CADDY Wire Basket Tray Washer Support and nVent CADDY Wire Basket Tray Ground Splice

Utilize with the nVent CADDY Wire Basket Tray C Bracket for multi-tier cable tray runs


Materiale: Stål
Finish: Electrogalvanized



SPECIFIKATIONER

Katalognummer	Farve	Height (H)	Width (W)	Length (L)	Hole Size (HS)	Unit Weight
WBTLBRKT12		127 mm	41.4 mm	350.52mm	7.16 mm	0.712 kg
WBTLBRKT12BA	Black	127 mm	41.4 mm	198.12mm	7.16 mm	0.712 kg
WBTLBRKT4		127 mm	41.4 mm	96.52mm	7.16 mm	0.395 kg
WBTLBRKT4BA	Black	127 mm	41.4 mm	452.12mm	7.16 mm	0.395 kg
WBTLBRKT6		127 mm	41.4 mm	452.12mm	7.16 mm	0.476 kg
WBTLBRKT6BA	Black	127 mm	41.4 mm	502.92mm	7.16 mm	0.476 kg
WBTLBRKT8		127 mm	41.4 mm	553.72mm	7.16 mm	0.553 kg
WBTLBRKT8BA	Black	127 mm	41.4 mm	553.72mm	7.16 mm	0.553 kg

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unkladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDDT

