


Wire Basket Tray PreForm Intersection



The nVent CADDY Wire Basket Tray PreForm Intersection is a precision-engineered solution designed to streamline cable tray installations at multi-pathway junctions. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Intersection delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Intersection significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

FUNKTIONER

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in multiple directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems

Materiale: Stål
Finish: Pregalvanized; Polyurethane



SPECIFIKATIONER

Table 1/2


Katalognummer	Farve	Height (H)	Width (W)	Length (L)	Hole Size (HS)	Radius (R)
WBTI2X12		50.8 mm	711.2 mm	711.2mm	19.05 mm	94.64mm
WBTI2X12BA	Black	50.8 mm	711.2 mm	711.2mm	19.05 mm	94.64mm
WBTI2X18		50.8 mm	861.06 mm	861.06mm	19.05 mm	94.64mm
WBTI2X18BA	Black	50.8 mm	861.06 mm	861.06mm	19.05 mm	94.64mm
WBTI2X24		50.8 mm	1016 mm	1016mm	19.05 mm	94.64mm
WBTI2X24BA	Black	50.8 mm	1016 mm	1016mm	19.05 mm	94.64mm
WBTI2X4		50.8 mm	511.48 mm	511.48mm		94.64mm
WBTI2X4BA	Black	50.8 mm	511.48 mm	511.48mm		94.64mm
WBTI2X6		50.8 mm	561.34 mm	561.34mm		94.64mm

Katalognummer	Farve	Height (H)	Width (W)	Length (L)	Hole Size (HS)	Radius (R)
WBTI2X6BA	Black	50.8 mm	561.34 mm	561.34mm		94.64mm
WBTI2X8		50.8 mm	612.14 mm	612.14mm		94.64mm
WBTI2X8BA	Black	50.8 mm	612.14 mm	612.14mm		94.64mm

Table 2/2

Katalognummer	Unit Weight	Certificeringer
WBTI2X12	3.175 kg	UL, CE, nVent CADDY Wire Basket Tray System, cUL
WBTI2X12BA	3.175 kg	CE, nVent CADDY Wire Basket Tray System
WBTI2X18	5.443 kg	CE, nVent CADDY Wire Basket Tray System, UL, cUL
WBTI2X18BA	5.443 kg	CE, nVent CADDY Wire Basket Tray System
WBTI2X24	8.165 kg	UL, CE, nVent CADDY Wire Basket Tray System, cUL
WBTI2X24BA	8.165 kg	CE, nVent CADDY Wire Basket Tray System
WBTI2X4	0.907 kg	CE, nVent CADDY Wire Basket Tray System, UL, cUL
WBTI2X4BA	0.907 kg	CE, nVent CADDY Wire Basket Tray System
WBTI2X6	1.361 kg	cUL, CE, nVent CADDY Wire Basket Tray System, UL
WBTI2X6BA	1.361 kg	CE, nVent CADDY Wire Basket Tray System
WBTI2X8	2.268 kg	UL, cUL, CE, nVent CADDY Wire Basket Tray System
WBTI2X8BA	2.268 kg	CE, nVent CADDY Wire Basket Tray System

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

