

Lakeret glasdør | Gulvskabe, DNG



De elektriske komponenter kan ses, når døren er lukket, hvilket holder uautoriseret personale ude og opretholder beskyttelsen mod indtrængning.

FUNKTIONER

Beskrivelse: Glasdør monteret med klart sikkerhedsglas til observation af skabets indhold. Udstyret med dobbelt-bit 3 mm låsesystem og dørramme. Alt ekstraudstyr i låseprogrammet kan benyttes. Kompatibelt med kombinerbare og kompakte skabsserier.

Materiale: Ramme: 2 mm stålplade. Synsområde: 4 mm klart sikkerhedsglas.

Overfladebehandling: Strukturpulvermaling. RAL 7035.

Tæthedsgrad: Overholder IP 55 | TYPE 12 | IK 07.

Pakke størrelse: 1 stk.

Monteringskrav: Anvend hængsel sæt DNMK01 hvis dør ikke tidligere har været monteret.

Materiale:	Lakeret Stål
Finish:	Struktur Pulvermaling
Farve:	Light Gray
Farvekode:	RAL 7035
Tykkelse:	2mm

SPECIFIKATIONER

Katalognummer	Artikelnummer	Højde	Bredde	Dybde	Window Size	Produktfamilie
DNG1106R5	DNG1106R5	1082mm	593mm	17mm	876 x 415mm	Free-Standing
DNG1206R5	DNG1206R5	1182mm	593mm	17mm	976 x 415mm	Free-Standing
DNG1208R5	DNG1208R5	1182mm	793mm	17mm	976 x 615mm	Free-Standing
DNG1406R5		1382mm	593mm	17mm	1176 x 415mm	Free-Standing
DNG1408R5		1382mm	793mm	17mm	1176 x 615mm	Free-Standing

Katalognummer	Artikelnummer	Højde	Bredde	Dybde	Window Size	Produktfamilie
DNG1606R5		1582mm	593mm	17mm	1376 x 415mm	Free-Standing
DNG1608R5		1582mm	793mm	17mm	1376 x 615mm	Free-Standing
DNG1806R5		1782mm	593mm	17mm	1576 x 415mm	Free-Standing
DNG1808R5		1782mm	793mm	17mm	1576 x 615mm	Free-Standing
DNG2006R5		1982mm	593mm	17mm	1776 x 415mm	Free-Standing
DNG2008R5		1982mm	793mm	17mm	1776 x 615mm	Free-Standing
DNG2010R5		1982mm	992mm	17mm		Free-Standing
DNG2206R5		2182mm	593mm	17mm	1976 x 415mm	Free-Standing
DNG2208R5		2182mm	793mm	17mm	1976 x 615mm	Free-Standing

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.