

Gennemsigtige døre | Vægskabe, ADT



De elektriske komponenter kan ses, når døren er lukket, hvilket holder uautoriseret personale ude og opretholder beskyttelsen mod indtrængning.

FUNKTIONER

Beskrivelse: Til erstatning af standarddøren. Viser tydeligt de komponenter, som er installeret inde i skabet. Kan bruges med alt udstyr fra låseprogrammet.

Materiale: 1.2 mm lakeret stål / 1.5 mm for skabe med en højde eller bredde 500 mm eller større / 2 mm til skabe med en højde eller bredde på 800 mm eller derover, samt 3 mm klart akrylglas.

Overfladebehandling: RAL 7035 struktur pulvermaling.

Tæthedsgad: I overensstemmelse med IP55, IK07.

Pakke størrelse: 1 stk.

Materiale: Lakeret Stål
Finish: Struktur Pulvermaling
Farve: Light Gray
Farvekode: RAL 7035

SPECIFIKATIONER

Katalognummer	Højde	Bredde	Dybde	Tykkelse	Antal låse	Window Size
ADT03025R5	295mm	245mm	15mm	1.2mm	1	159 x 93mm
ADT03030R5	295mm	294mm	15mm	1.2mm	1	159 x 143mm
ADT04030R5	395mm	294mm	15mm	1.2mm	1	259 x 143mm
ADT04040R5	395mm	394mm	15mm	1.2mm	1	259 x 143mm
ADT05030R5	495mm	294mm	15mm	1.5mm	1	359 x 143mm
ADT05040R5	495mm	394mm	15mm	1.5mm	1	359 x 243mm
ADT06040R5	595mm	394mm	15mm	1.5mm	2	459 x 243mm
ADT06050R5	595mm	495mm	15mm	1.5mm	2	459 x 343mm
ADT06060R5	595mm	595mm	15mm	1.5mm	2	459 x 443mm
ADT07050R5	695mm	495mm	15mm	1.5mm	2	559 x 343mm
ADT08060R5	795mm	595mm	15mm	2mm	2	659 x 443mm
ADT10060R5	995mm	595mm	15mm	2mm	1	859 x 427mm

Katalognummer	Højde	Bredde	Dybde	Tykkelse	Antal låse	Window Size
ADT10080R5	995mm	795mm	15mm	2mm	1	859 x 627mm
ADT12060R5	1195mm	595mm	15mm	2mm	1	1059 x 427mm
ADT12080R5	1195mm	795mm	15mm	2mm	1	1059 x 627mm

YDERLIGERE PRODUKTOPLYSNINGER

* 3-punkts espagnoletlås. Ikke velegnet til AFS.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.