


Collar Screw, Cross Recess/Slotted



Integrated load spreading, replaces separate washer.
Improved joint consistency (less variation from washer misalignment) Better vibration resistance, especially with serrated collars

FUNKTIONER

For assembly of partial width front panels and plug-in units

For EuropacPRO and RatiopacPRO

Cross Recess / Slotted combines advantages of both imprints: it offers a high level of torque to achieve quick and easy installation and enhances rotational leverage. It is convenient to use while offering universal tool compatibility.

Type: Screw
Product Type: Screw



SPECIFIKATIONER

Table 1/2

Katalognummer	Diameter	Length	Materiale	Finish	Pakke mængde	Thread Size
21102-026	2.5mm	12.3mm	Stål	Nickel Plated	100	M2.5
21101-102		12.3mm	Stål	Zinc Top Coat	100	M2.5
21101-906		12.3mm	Stainless Steel		100	M2.5
21101-101		12.3mm	Stål	Nickel Plated	100	M2.5
21101-323		11mm			100	M2.5

Table 2/2

Katalognummer	Dybde	Højde	Bredde	Works With	Thread Type	Torque	Certificeringer
21102-026				Frame Type Plug-In Unit, Cassettes		0.3N·m	
21101-102	14.3mm	5mm	5mm	Front Panels	Metric	0.3N·m	RoHS
21101-906				Front Panels		0.3N·m	RoHS
21101-101	14.3mm	5mm	5mm	Front Panels	Metric	0.3N·m	RoHS
21101-323				Front Panels			

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE