

Front/bag sokkel rustfrit stål, PFS

Denne sokkel af rustfrit stål muliggør kabelføring uden begrænsninger. Det bliver nemt at montere kabler, da soklen skaber ekstra plads under skabet.



FUNKTIONER

Beskrivelse: Front og bag sokkel sektioner. Til kabling uden begrænsninger og iht VDE 0113 standard. Soklen indeholder 4 hjørner med aftagelig frontdæksel. Sidepanelerne PSS skal bestilles separat. Udført i hhv. 100 mm og 200 mm højde. 200 mm høje sokler leveres med et bagdæksel til kabelføring og består af to aftagelige paneler 100 mm høje. Frontdækslet er et enkelt panel 200 mm højt. Alle paneler har dobbelt retur på hvert panel for ekstra styrke.

Materiale: AISI 304 / AISI 316L slebet rustfrit stål. Hjørner 2 mm og paneler 1.5 mm.

Overfladebehandling: 400 slebet rustfrit stål.

Pakke størrelse: 1x front sokkel og 1x bag sokkel med monteringsmateriale.

Monteringskrav: Tilføj sidepaneler PSS for en komplet sokkel.

Finish: Poleret
Tykkelse: 1.5mm

SPECIFIKATIONER

Katalognummer	Højde	Bredde	Dybde	Produktfamilie	Materiale	Enclosure Material
PFS1120	100mm	1200mm	60mm	Free-Standing	Stainless Steel 304	Lakeret Stål
PFS2120	200mm	1200mm	60mm	Free-Standing	Stainless Steel 304	Lakeret Stål
PFS1080	100mm	800mm	60mm	Free-Standing	Stainless Steel 304	Lakeret Stål
PFS2080	200mm	800mm	60mm	Free-Standing	Stainless Steel 304	Lakeret Stål
PFS1060	100mm	600mm	60mm	Free-Standing	Stainless Steel 304	Lakeret Stål
PFS2060	200mm	600mm	60mm	Free-Standing	Stainless Steel 304	Lakeret Stål
PFS1100	100mm	1000mm	60mm	Free-Standing	Stainless Steel 304	Lakeret Stål
PFS2100	200mm	1000mm	60mm	Free-Standing	Stainless Steel 304	Lakeret Stål
PFS1060-316	100mm	600mm	60mm	Free-Standing	Stainless Steel 316	Lakeret Stål
PFS1080-316	100mm	800mm	60mm	Free-Standing	Stainless Steel 316	Lakeret Stål

Katalognummer	Højde	Bredde	Dybde	Produktfamilie	Materiale	Enclosure Material
PFS1100-316	100mm	1000mm	60mm	Free-Standing	Stainless Steel 316	Lakeret Stål
PFS1120-316	100mm	1200mm	60mm	Free-Standing	Stainless Steel 316	Lakeret Stål
PFS2060-316	200mm	600mm	60mm	Free-Standing	Stainless Steel 316	Lakeret Stål
PFS2080-316	200mm	800mm	60mm	Free-Standing	Stainless Steel 316	Lakeret Stål
PFS2100-316	200mm	1000mm	60mm	Free-Standing	Stainless Steel 316	Lakeret Stål
PFS2120-316	200mm	1200mm	60mm	Free-Standing	Stainless Steel 316	Lakeret Stål

YDERLIGERE PRODUKTOPLYSNINGER

For skabe i 1600 mm bredde anvendes 2x800 mm sokler.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.