


# Monteringsplade i delvis højde | Gulvskabe, MPP



Denne lille monteringsplade fylder kun en del af skabet, og er ideel, når der kræves mere monteringsplads til andre komponenter, som ikke kræver en monteringsplade. Den kan udstyres komplet, før den sættes på plads af en enkelt person.

## FUNKTIONER

Beskrivelse: Monteres direkte på skabsrammen eller på klik-ind-profilerne (CLPK). Det specielt designede beslag gør montering nemmere. Kan monteres i enhver højde- eller dybdeposition inden for 25 mm hulmønster. Passende størrelser kan også anvendes på siderne af skabet.

Materiale: 3 mm galvaniseret stål.

Pakke størrelse: 1 plade med monteringstilbehør.

Monteringskrav: Tilføj CLPK for dybdejustering.

Bemærk: MPP kan monteres i begge retninger.

**Materiale:** Lakeret Stål  
**Finish:** Galvaniseret  
**Tykkelse:** 3mm

## SPECIFIKATIONER

| Katalognummer | Højde | Bredde | Dybde | Kompatibel kabinetshøjde | Kompatibel kabinetsbredde | Enclosure Material |
|---------------|-------|--------|-------|--------------------------|---------------------------|--------------------|
| MPP0404       | 294mm | 294mm  | 25mm  | 400mm                    | 400mm                     | Lakeret Stål       |
| MPP0405       | 294mm | 394mm  | 25mm  | 400mm                    | 500mm                     | Lakeret Stål       |
| MPP0604       | 494mm | 294mm  | 25mm  | 600mm                    | 400mm                     | Lakeret Stål       |
| MPP0605       | 494mm | 394mm  | 25mm  | 600mm                    | 500mm                     | Lakeret Stål       |
| MPP0606       | 494mm | 494mm  | 25mm  | 600mm                    | 600mm                     | Lakeret Stål       |
| MPP0608       | 494mm | 694mm  | 25mm  | 600mm                    | 800mm                     | Lakeret Stål       |
| MPP0610       | 494mm | 894mm  | 25mm  | 600mm                    | 1000mm                    | Lakeret Stål       |
| MPP0804       | 694mm | 294mm  | 25mm  | 800mm                    | 400mm                     | Lakeret Stål       |
| MPP0805       | 694mm | 394mm  | 25mm  | 800mm                    | 500mm                     | Lakeret Stål       |
| MPP0808       | 694mm | 694mm  | 25mm  | 800mm                    | 800mm                     | Lakeret Stål       |

| Katalognummer | Højde  | Bredde | Dybde | Kompatibel kabinetshøjde | Kompatibel kabinetsbredde | Enclosure Material |
|---------------|--------|--------|-------|--------------------------|---------------------------|--------------------|
| MPP1004       | 894mm  | 294mm  | 25mm  | 1000mm                   | 400mm                     | Lakeret Stål       |
| MPP1008       | 894mm  | 694mm  | 25mm  | 1000mm                   | 800mm                     | Lakeret Stål       |
| MPP1204       | 1094mm | 294mm  | 25mm  | 1200mm                   | 400mm                     | Lakeret Stål       |
| MPP1206       | 1094mm | 494mm  | 25mm  | 1200mm                   | 600mm                     | Lakeret Stål       |

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.