

Regntag, MSST



Et regntag af rustfrit stål giver ly vha. et skråtag og beskytter de monterede komponenter mod opsamlet vand, der drypper ind i skabet, når døren åbnes.

FUNKTIONER

Beskrivelse: Skal monteres som ekstra beskyttelse på skabe i rustfrit stål. Skabets top er let skrånende og udstyret med drypliste.

Materiale: 1,5 mm rustfrit stål AISI 304 / AISI 316L.

Overfladebehandling: 400 slebet rustfrit stål.

Finish: Poleret

Tykkelse: 1.5mm

SPECIFIKATIONER

Table 1/2

Katalognummer	Højde	Bredde	Dybde	Materiale	Produktfamilie	Enclosure Material
MSST0640N	400mm	600mm	72mm	Stainless Steel 304	Free-Standing	Lakeret Stål
MSST0640N-316	400mm	600mm	72mm	Stainless Steel 316	Free-Standing	Lakeret Stål
MSST0650N	500mm	600mm	72mm	Stainless Steel 304	Free-Standing	Lakeret Stål
MSST0650N-316	500mm	600mm	72mm	Stainless Steel 316	Free-Standing	Lakeret Stål
MSST0660N	600mm	600mm	72mm	Stainless Steel 304	Free-Standing	Lakeret Stål
MSST0660N-316	600mm	600mm	72mm	Stainless Steel 316	Free-Standing	Lakeret Stål
MSST0840N	400mm	800mm	72mm	Stainless Steel 304	Free-Standing	Lakeret Stål
MSST0840N-316	400mm	800mm	72mm	Stainless Steel 316	Free-Standing	Lakeret Stål
MSST0850N	500mm	800mm	72mm	Stainless Steel 304	Free-Standing	Lakeret Stål
MSST0850N-316	500mm	800mm	72mm	Stainless Steel 316	Free-Standing	Lakeret Stål
MSST0860N	600mm	800mm	72mm	Stainless Steel 304	Free-Standing	Lakeret Stål
MSST0860N-316	600mm	800mm	72mm	Stainless Steel 316	Free-Standing	Lakeret Stål

Katalognummer	Højde	Bredde	Dybde	Materiale	Produktfamilie	Enclosure Material
MSST1040N	400mm	1000mm	72mm	Stainless Steel 304	Free-Standing	Lakeret Stål
MSST1040N-316	400mm	1000mm	72mm	Stainless Steel 316	Free-Standing	Lakeret Stål
MSST1050N	500mm	1000mm	72mm	Stainless Steel 304	Free-Standing	Lakeret Stål
MSST1050N-316	500mm	1000mm	72mm	Stainless Steel 316	Free-Standing	Lakeret Stål
MSST1060N	600mm	1000mm	72mm	Stainless Steel 304	Free-Standing	Lakeret Stål
MSST1060N-316	600mm	1000mm	72mm	Stainless Steel 316	Free-Standing	Lakeret Stål
MSST1240N	400mm	1200mm	72mm	Stainless Steel 304	Free-Standing	Lakeret Stål
MSST1240N-316	400mm	1200mm	72mm	Stainless Steel 316	Free-Standing	Lakeret Stål

Table 2/2

Katalognummer	Højde	Bredde	Dybde	Materiale	Produktfamilie	Enclosure Material
MSST1250N	500mm	1200mm	72mm	Stainless Steel 304	Free-Standing	Lakeret Stål
MSST1250N-316	500mm	1200mm	72mm	Stainless Steel 316	Free-Standing	Lakeret Stål
MSST1260N	600mm	1200mm	72mm	Stainless Steel 304	Free-Standing	Lakeret Stål
MSST1260N-316	600mm	1200mm	72mm	Stainless Steel 316	Free-Standing	Lakeret Stål
MSST1640N	400mm	1600mm	72mm	Stainless Steel 304	Free-Standing	Lakeret Stål
MSST1640N-316	400mm	1600mm	72mm	Stainless Steel 316	Free-Standing	Lakeret Stål

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

