

# Sidesokler, PSS



Sokkelsidepanelerne anvendes til at lukke hulrummet under skabet, hvis det er nødvendigt.

## FUNKTIONER

Beskrivelse: Sidepaneler til afdækning af åbninger i siderne af PFS-soklen. Dobbeltbukkede paneler for maksimal styrke. Passer til udvalget af kombinerbare og kompakte gulvskabe i rustfrit stål.

Materiale: Slebet rustfrit stål af type AISI 304/AISI 316L.  
Paneller: 1.5 mm.

Overfladebehandling: 400 slebet rustfrit stål.

Pakke størrelse: 2 paneler. Monteringstilbehør leveres sammen med PFS.

## SPECIFIKATIONER

| Katalognummer | Højde | Bredde | Dybde | Produktfamilie | Materiale           | Enclosure Material            |
|---------------|-------|--------|-------|----------------|---------------------|-------------------------------|
| PSS1040       | 100mm | 400mm  | 27mm  | Free-Standing  | Stainless Steel 304 | Lakeret Stål, Stainless Steel |
| PSS2040       | 200mm | 400mm  | 27mm  | Free-Standing  | Stainless Steel 304 | Lakeret Stål, Stainless Steel |
| PSS1050       | 100mm | 500mm  | 27mm  | Free-Standing  | Stainless Steel 304 | Lakeret Stål, Stainless Steel |
| PSS2050       | 200mm | 500mm  | 27mm  | Free-Standing  | Stainless Steel 304 | Lakeret Stål, Stainless Steel |
| PSS1060       | 100mm | 600mm  | 27mm  | Free-Standing  | Stainless Steel 304 | Lakeret Stål, Stainless Steel |
| PSS2060       | 200mm | 600mm  | 27mm  | Free-Standing  | Stainless Steel 304 | Lakeret Stål, Stainless Steel |
| PSS1040-316   | 100mm | 400mm  | 27mm  | Free-Standing  | Stainless Steel 316 | Lakeret Stål, Stainless Steel |
| PSS1050-316   | 100mm | 500mm  | 27mm  | Free-Standing  | Stainless Steel 316 | Lakeret Stål, Stainless Steel |
| PSS1060-316   | 100mm | 600mm  | 27mm  | Free-Standing  | Stainless Steel 316 | Lakeret Stål, Stainless Steel |
| PSS2040-316   | 200mm | 400mm  | 27mm  | Free-Standing  | Stainless Steel 316 | Lakeret Stål, Stainless Steel |
| PSS2050-316   | 200mm | 500mm  | 27mm  | Free-Standing  | Stainless Steel 316 | Lakeret Stål, Stainless Steel |
| PSS2060-316   | 200mm | 600mm  | 27mm  | Free-Standing  | Stainless Steel 316 | Lakeret Stål, Stainless Steel |
| PSS1080-316   | 100mm | 800mm  | 27mm  | Free-Standing  | Stainless Steel 316 | Lakeret Stål, Stainless Steel |
| PSS1100-316   | 100mm | 999mm  | 27mm  | Free-Standing  | Stainless Steel 316 | Lakeret Stål, Stainless Steel |
| PSS2080-316   | 200mm | 800mm  | 27mm  | Free-Standing  | Stainless Steel 316 | Lakeret Stål, Stainless Steel |
| PSS2100-316   | 200mm | 999mm  | 27mm  | Free-Standing  | Stainless Steel 316 | Lakeret Stål, Stainless Steel |

## ADVARSEL

---

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.