

PMC Mezzanine Front Panel, Untreated, With EMC Shielding



Mezzanine front panel is fitted into PMC front panel cut-outs. Available in different treatments. For O-ring EMC gasket.

FUNKTIONER

Mezzanine front panel is fitted into PMC front panel cut-outs

EMC shielding with conductive O-ring

Product Type: Front Panel
Type: Front Panel without Handle
EMC Shielding: Yes



SPECIFIKATIONER

Table 1/2

Katalognummer	Pakke mængde	Accessory Type	Mounting	Gasket Type	Front Finish	Rear Finish
20835-598	1	Front panel	Screw-on Front	O-Ring EMC	Anodized	Conductive
20835-922	1		Screw-on Front		Chrome Plated	Chrome Plated
20835-890	1		Screw-on Front			
20835-923	1		Screw-on Front		Chrome Plated	Chrome Plated
20835-889	1	Front panel	Screw-on Front	O-Ring EMC	Anodized	Conductive
20835-893	10		Screw-on Front		Chrome Plated	Chrome Plated
20835-928	10		Screw-on Front		Anodized	Conductive
20835-924	10		Screw-on Front		Chrome Plated	Chrome Plated

Table 2/2

Katalognummer	Treated Edges	Complies With	Dybde	Finish	Højde	Materiale	Bredde
20835-598	No	PMC Mezzanine, IEEE P1386	2.5mm	Anodized	74mm	Aluminium	12.7mm
20835-922	Yes	PMC Mezzanine, IEEE P1386			74mm	Zinc	12.7mm
20835-890	No	PMC Mezzanine, IEEE P1386			74mm	Zinc	12.7mm
20835-923	Yes	PMC Mezzanine, IEEE P1386			74mm	Zinc	12.7mm
20835-889	No	PMC Mezzanine, IEEE P1386	2.5mm	Anodized	74mm	Aluminium	12.7mm
20835-893	Yes	PMC Mezzanine, IEEE P1386			74mm	Zinc	12.7mm
20835-928	No	PMC Mezzanine, IEEE P1386			74mm	Zinc	12.7mm
20835-924	Yes	PMC Mezzanine, IEEE P1386			74mm	Zinc	12.7mm

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE