


Halsschraube, Kreuzschlitz/Schlitz



Integrated load spreading, replaces separate washer.
Improved joint consistency (less variation from washer misalignment) Better vibration resistance, especially with serrated collars

MERKMALE

For assembly of partial width front panels and plug-in units

For EuropacPRO and RatiopacPRO

Cross Recess / Slotted combines advantages of both imprints: it offers a high level of torque to achieve quick and easy installation and enhances rotational leverage. It is convenient to use while offering universal tool compatibility.

Produkttyp: Schraube

Typ: Schraube



SPEZIFIKATIONEN

Table 1/3

Katalognummer	Durchmesser	Länge	Material	Oberfläche	Anzahl Verpackungen	Gewindegröße
21101-101		12.3mm	Stahl	Vernickelt	100	M2.5
21101-906		12.3mm	Edelstahl		100	M2.5
21101-102		12.3mm	Stahl	Zinc Plated, Black	100	M2.5
21101-323		11mm			100	M2.5
21102-026	2.5mm	12.3mm	Stahl	Vernickelt	100	M2.5

Table 2/3

Katalognummer	Tiefe	Höhe	Breite	Passt zu	Gewindelänge	Gewindeart
21101-101	14.3mm	5mm	5mm	Frontplatten	12.3mm	Metrisch
21101-906				Frontplatten	12.3mm	
21101-102	14.3mm	5mm	5mm	Frontplatten	12.3mm	Metrisch
21101-323				Frontplatten		
21102-026				Rahmentyp-Steckbaugruppe, Kassetten	3mm	

Table 3/3

Katalognummer	Drehmoment	Zertifizierungen
21101-101	0.3N·m	RoHS
21101-906	0.3N·m	RoHS
21101-102	0.3N·m	RoHS
21101-323	0.3N·m	
21102-026	0.3N·m	

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

