

# Wire Basket Tray Independent Underfloor Support, 101x558mm, Pregalvanized

## KATALOGNUMMER

### WBTUS04



The nVent CADDY Wire Basket Tray Underfloor Support provides a reliable method for routing wire basket trays beneath the floor with independent structural support. This component is ideal for installations requiring low-voltage cabling to pass under cabinets or equipment.

Engineered for stability and simplicity, the underfloor support system eliminates the need for complex framing. It braces the tray directly beneath raised floors, allowing for clean, unobtrusive cable pathways that preserve floor space and reduce visual clutter. This is especially valuable in data centers, control rooms, and other high-density environments where cable organization and accessibility are critical.

The Support integrates seamlessly with the broader nVent CADDY Wire Basket Tray System, ensuring compatibility with shaped and round wire tray profiles. Its design accommodates standard fasteners and finishes, including pre-galvanized, zinc electroplate, and powder coat options, making it adaptable to a wide range of project specifications.

## MERKMALE

Designed to be used with the nVent CADDY Wire Basket Tray Washer Support and nVent CADDY Wire Basket Tray Ground Splice

Maintains a fixed and secure distance from the ground to ensure safety and accessibility

Available in a range of sizes to match wire basket tray design

Fixed height ensures a level installation

## PRODUKTMERKMALE

Material: Stahl

Oberfläche: Vorverzinkung

Höhe (H): 32 mm

Länge (L): 767mm


Länge 1 (L1): 560.78 mm

Breite (W): 235 mm

Lochgröße (HS): 14.3 mm

Stückgewicht: 0.862 kg

## DIAGRAMME



## WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter [www.nVent.com](http://www.nVent.com) sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.

### Nordamerika

+1.800.753.9221

Option 1 – Kundendienst

Option 2 – Technischer

Support

### Europa

Niederlande:

+31 800-0200135

Frankreich:

+33 800 901 793

### Europa

Deutschland:

800 1890272

Sonstige Länder:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. Alle Marken und Logos von nVent sind Eigentum der nVent Services GmbH oder ihrer Tochtergesellschaften oder durch sie lizenziert. Alle übrigen Marken sind Eigentum ihrer jeweiligen Inhaber. nVent behält sich das Recht vor, ohne Vorankündigung Änderungen vorzunehmen.

Dieses Dokument ist systemgeneriert.

