


Wire Basket Tray PreForm Intersection



The nVent CADDY Wire Basket Tray PreForm Intersection is a precision-engineered solution designed to streamline cable tray installations at multi-pathway junctions. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Intersection delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Intersection significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

MERKMALE

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in multiple directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems

Material: Stahl
Oberfläche: Vorverzinkung; Polyurethan



SPEZIFIKATIONEN

Table 1/2


Katalognummer	Farbe	Höhe (H)	Breite (W)	Länge (L)	Lochgröße (HS)	Radius (R)
WBTI2X12		50.8 mm	711.2 mm	711.2mm	19.05 mm	94.64mm
WBTI2X12BA	Schwarz	50.8 mm	711.2 mm	711.2mm	19.05 mm	94.64mm
WBTI2X18		50.8 mm	861.06 mm	861.06mm	19.05 mm	94.64mm
WBTI2X18BA	Schwarz	50.8 mm	861.06 mm	861.06mm	19.05 mm	94.64mm
WBTI2X24		50.8 mm	1016 mm	1016mm	19.05 mm	94.64mm
WBTI2X24BA	Schwarz	50.8 mm	1016 mm	1016mm	19.05 mm	94.64mm
WBTI2X4		50.8 mm	511.48 mm	511.48mm		94.64mm
WBTI2X4BA	Schwarz	50.8 mm	511.48 mm	511.48mm		94.64mm
WBTI2X6		50.8 mm	561.34 mm	561.34mm		94.64mm

Katalognummer	Farbe	Höhe (H)	Breite (W)	Länge (L)	Lochgröße (HS)	Radius (R)
WBTI2X6BA	Schwarz	50.8 mm	561.34 mm	561.34mm		94.64mm
WBTI2X8		50.8 mm	612.14 mm	612.14mm		94.64mm
WBTI2X8BA	Schwarz	50.8 mm	612.14 mm	612.14mm		94.64mm

Table 2/2

Katalognummer	Stückgewicht	Zertifizierungen
WBTI2X12	3.175 kg	UL, CE, nVent CADDY Wire Basket Tray System, cUL
WBTI2X12BA	3.175 kg	CE, nVent CADDY Wire Basket Tray System
WBTI2X18	5.443 kg	CE, nVent CADDY Wire Basket Tray System, UL, cUL
WBTI2X18BA	5.443 kg	CE, nVent CADDY Wire Basket Tray System
WBTI2X24	8.165 kg	UL, CE, nVent CADDY Wire Basket Tray System, cUL
WBTI2X24BA	8.165 kg	CE, nVent CADDY Wire Basket Tray System
WBTI2X4	0.907 kg	CE, nVent CADDY Wire Basket Tray System, UL, cUL
WBTI2X4BA	0.907 kg	CE, nVent CADDY Wire Basket Tray System
WBTI2X6	1.361 kg	cUL, CE, nVent CADDY Wire Basket Tray System, UL
WBTI2X6BA	1.361 kg	CE, nVent CADDY Wire Basket Tray System
WBTI2X8	2.268 kg	UL, cUL, CE, nVent CADDY Wire Basket Tray System
WBTI2X8BA	2.268 kg	CE, nVent CADDY Wire Basket Tray System

DIAGRAMME



WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.

Nordamerika

+1.800.753.9221

Option 1 – Kundendienst

Option 2 – Technischer

Support

Europa

Niederlande:

+31 800-0200135

Frankreich:

+33 800 901 793

Europa

Deutschland:

800 1890272

Sonstige Länder:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. Alle Marken und Logos von nVent sind Eigentum der nVent Services GmbH oder ihrer Tochtergesellschaften oder durch sie lizenziert. Alle übrigen Marken sind Eigentum ihrer jeweiligen Inhaber. nVent behält sich das Recht vor, ohne Vorankündigung Änderungen vorzunehmen.

Dieses Dokument ist systemgeneriert.

