

C-ES Cable to Vertical Flange Clamp



FEATURES

Supports single run of cable

Attaches to beam flanges, angle iron, joists and other structural supports

Material: Steel
Finish: Hot-Dip Galvanized

SPECIFICATIONS



Catalog Number	Article Number	Outer Diameter (OD)	A	Torque (TQ)
C12ES	337000	6 - 12 mm	43 mm	2 N·m
C16ES	337010	12 - 16 mm	43 mm	2 N·m
C20ES	337020	16 - 20 mm	43 mm	2 N·m
C24ES	337030	20 - 24 mm	43 mm	2 N·m
C28ES	337040	24 - 28 mm	43 mm	2 N·m
C32ES	337050	28 - 32 mm	43 mm	2 N·m
C36ES	337060	32 - 36 mm	43 mm	2 N·m
C40ES	337070	36 - 40 mm	43 mm	2 N·m
C44ES	337080	40 - 44 mm	43 mm	4 N·m
C48ES	337090	44 - 48 mm	43 mm	4 N·m
C52ES	337100	48 - 52 mm	43 mm	4 N·m
C56ES	337110	52 - 56 mm	43 mm	4 N·m
C60ES	337120	56 - 60 mm	43 mm	4 N·m

Catalog Number	Article Number	Outer Diameter (OD)	A	Torque (TQ)
C64ES	337130	60 - 64 mm	43 mm	4 N·m
C70ES	337140	64 - 70 mm	43 mm	4 N·m
C76ES	337150	70 - 76 mm	43 mm	4 N·m
C82ES	337160	76 - 82 mm	43 mm	4 N·m

ADDITIONAL PRODUCT DETAILS

Screw is electrogalvanized on clamps that have an outer diameter of 40 mm or less.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDDT

