

# Locking System For Lift Handles, LHC

The locking inserts and cylinders can be mounted independently in the lift handle, which means many combinations can be created. This reduces the number of handles to be stocked.



## FEATURES

Description: Profile half cylinder locks. To be used in the lift handles LHC.

Pack quantity: 1 piece.

**Color:** Black Gray  
**Finish:** Smooth Matte

## SPECIFICATIONS

| Catalog Number | Article Number | Height | Width | Depth | Key Type                                            | Key Code |
|----------------|----------------|--------|-------|-------|-----------------------------------------------------|----------|
| LHC534         | LHC534         | 37mm   | 23mm  | 41mm  | Adapter for other profile half cylinders (DIN18252) |          |
| LHC5213121E    | LHC5213121E    | 37mm   | 23mm  | 41mm  | Ronis                                               | 3121E    |
| LHC526         | LHC526         | 37mm   | 23mm  | 41mm  | Triangle 7 mm                                       |          |
| LHC527         | LHC527         | 37mm   | 23mm  | 41mm  | Triangle 8 mm                                       |          |
| LHC528         | LHC528         | 37mm   | 23mm  | 41mm  | Double-bit 3 mm                                     |          |
| LHC524         | LHC524         | 37mm   | 23mm  | 41mm  | Square 8 mm                                         |          |
| LHC531         | LHC531         | 37mm   | 23mm  | 41mm  | Lock insert slotted 2x4 mm                          |          |
| LHC536         | LHC536         | 37mm   | 23mm  | 41mm  | Push button only                                    |          |
| LHC5212132E    | LHC5212132E    | 37mm   | 23mm  | 41mm  | Ronis                                               | 2132E    |
| LHC523         | LHC523         | 37mm   | 23mm  | 41mm  | Square 7 mm                                         |          |
| LHC533         | LHC533         | 37mm   | 23mm  | 41mm  | Cylinder N°E1 (VW), key excluded                    |          |
| LHC529         | LHC529         | 37mm   | 23mm  | 41mm  | Double-bit 5 mm                                     |          |
| LHC535         | LHC535         | 37mm   | 23mm  | 41mm  | Adapter for ASSA ABLOY and Trioving cylinders       |          |
| LHC521         | LHC521         | 37mm   | 23mm  | 41mm  | Ronis                                               | C21323   |
| LHC522         | LHC522         | 37mm   | 23mm  | 41mm  | Ronis                                               | C21323   |
| LHC530         | LHC530         | 37mm   | 23mm  | 41mm  | Daimler Benz                                        |          |

## ADDITIONAL PRODUCT DETAILS

---

\* Other key numbers available on request. \*\* Key numbers 333, 1333, EK333 and GX130 are equal. \*\*\* Order separate key LSMK for Square 8 mm and Triangle 8 mm.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**