

Partial Panels For Floor Standing Enclosures, DPP



Partial panels allow for many different, easily accessible, configurations of separate compartments within the enclosure. The panels are secured with screws, which ensures that it can only be removed by service personnel, to improve the operators safety.

FEATURES

Description: To divide the enclosure front into sections when used in conjunction with the horizontal divider CDH/CDHK when no door is required.

Material: 1.75 mm steel plate.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 54.

Pack quantity: 1 panel with mounting accessories.

Mounting requirements: Add CDH for MC frames and use CDHK for MK frames. Use DPC/DPCV for top and bottom panels.

Thickness: 1.75mm
Color: Light Gray
Material: Mild Steel
Finish: Powder Coated
Color Code: RAL 7035

SPECIFICATIONS

Catalog Number	Height	Width	Depth	Product Family	Enclosure Material
DPP02006R5	200mm	600mm	17mm	Free-Standing	Mild Steel

Catalog Number	Height	Width	Depth	Product Family	Enclosure Material
DPP03006R5	300mm	600mm	17mm	Free-Standing	Mild Steel
DPP01504R5	150mm	400mm	17mm	Free-Standing	Mild Steel
DPP03004R5	300mm	400mm	17mm	Free-Standing	Mild Steel
DPP01008R5	100mm	800mm	17mm	Free-Standing	Mild Steel
DPP03008R5	300mm	800mm	17mm	Free-Standing	Mild Steel
DPP02508R5	250mm	800mm	17mm	Free-Standing	Mild Steel
DPP01506R5	150mm	600mm	17mm	Free-Standing	Mild Steel
DPP01006R5	100mm	600mm	17mm	Free-Standing	Mild Steel
DPP04004R5	400mm	400mm	17mm	Free-Standing	Mild Steel
DPP02506R5	250mm	600mm	17mm	Free-Standing	Mild Steel
DPP01508R5	150mm	800mm	17mm	Free-Standing	Mild Steel
DPP04006R5	400mm	600mm	17mm	Free-Standing	Mild Steel
DPP02504R5	250mm	400mm	17mm	Free-Standing	Mild Steel
DPP02004R5	200mm	400mm	17mm	Free-Standing	Mild Steel
DPP01004R5	100mm	400mm	17mm	Free-Standing	Mild Steel
DPP04008R5	400mm	800mm	17mm	Free-Standing	Mild Steel
DPP02008R5	200mm	800mm	17mm	Free-Standing	Mild Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE