

Rain Hoods, MSST

A stainless steel rain hood provides shelter via a sloped roof and protects installed components from accumulated water dripping into the enclosure when the door is opened.

FEATURES

Description: To be fitted as extra protection on stainless steel enclosures. The roof is slightly sloped and has a dripstrip.

Material: 1.5 mm stainless steel AISI 304 / AISI 316L.

Finish: 400 pre-grained stainless steel.



Finish: Brushed

Thickness: 1.5mm

SPECIFICATIONS

Table 1/2

Catalog Number	Height	Width	Depth	Material	Product Family	Enclosure Material
MSST0640N	400mm	600mm	72mm	Stainless Steel 304	Free-Standing	Mild Steel
MSST0640N-316	400mm	600mm	72mm	Stainless Steel 316	Free-Standing	Mild Steel
MSST0650N	500mm	600mm	72mm	Stainless Steel 304	Free-Standing	Mild Steel
MSST0650N-316	500mm	600mm	72mm	Stainless Steel 316	Free-Standing	Mild Steel
MSST0660N	600mm	600mm	72mm	Stainless Steel 304	Free-Standing	Mild Steel
MSST0660N-316	600mm	600mm	72mm	Stainless Steel 316	Free-Standing	Mild Steel
MSST0840N	400mm	800mm	72mm	Stainless Steel 304	Free-Standing	Mild Steel
MSST0840N-316	400mm	800mm	72mm	Stainless Steel 316	Free-Standing	Mild Steel
MSST0850N	500mm	800mm	72mm	Stainless Steel 304	Free-Standing	Mild Steel
MSST0850N-316	500mm	800mm	72mm	Stainless Steel 316	Free-Standing	Mild Steel
MSST0860N	600mm	800mm	72mm	Stainless Steel 304	Free-Standing	Mild Steel
MSST0860N-316	600mm	800mm	72mm	Stainless Steel 316	Free-Standing	Mild Steel

Catalog Number	Height	Width	Depth	Material	Product Family	Enclosure Material
MSST1040N	400mm	1000mm	72mm	Stainless Steel 304	Free-Standing	Mild Steel
MSST1040N-316	400mm	1000mm	72mm	Stainless Steel 316	Free-Standing	Mild Steel
MSST1050N	500mm	1000mm	72mm	Stainless Steel 304	Free-Standing	Mild Steel
MSST1050N-316	500mm	1000mm	72mm	Stainless Steel 316	Free-Standing	Mild Steel
MSST1060N	600mm	1000mm	72mm	Stainless Steel 304	Free-Standing	Mild Steel
MSST1060N-316	600mm	1000mm	72mm	Stainless Steel 316	Free-Standing	Mild Steel
MSST1240N	400mm	1200mm	72mm	Stainless Steel 304	Free-Standing	Mild Steel
MSST1240N-316	400mm	1200mm	72mm	Stainless Steel 316	Free-Standing	Mild Steel

Table 2/2

Catalog Number	Height	Width	Depth	Material	Product Family	Enclosure Material
MSST1250N	500mm	1200mm	72mm	Stainless Steel 304	Free-Standing	Mild Steel
MSST1250N-316	500mm	1200mm	72mm	Stainless Steel 316	Free-Standing	Mild Steel
MSST1260N	600mm	1200mm	72mm	Stainless Steel 304	Free-Standing	Mild Steel
MSST1260N-316	600mm	1200mm	72mm	Stainless Steel 316	Free-Standing	Mild Steel
MSST1640N	400mm	1600mm	72mm	Stainless Steel 304	Free-Standing	Mild Steel
MSST1640N-316	400mm	1600mm	72mm	Stainless Steel 316	Free-Standing	Mild Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

