

# Collar Screw, Knurled Head Short Version



Integrated load spreading, replaces separate washer.  
Improved joint consistency (less variation from washer misalignment) Better vibration resistance, especially with serrated collars

## FEATURES

For assembly of partial width front panels

For EuropacPRO and RatiopacPRO

Knurled head for manual screwing / unscrewing

**Product Type:** Screw  
**Type:** Screw  
**Works With:** Front Panels



## SPECIFICATIONS

Table 1/2

| Catalog Number | Length | Material | Finish        | Package Quantity | Thread Size | Depth  |
|----------------|--------|----------|---------------|------------------|-------------|--------|
| 21101-749      | 12.3mm | Brass    | Nickel Plated | 100              | M2.5        | 18.3mm |
| 21100-268      | 11mm   | Brass    | Nickel Plated | 100              | M2.5        |        |
| 21101-106      | 11mm   | Steel    |               |                  | M2.5        |        |

Table 2/2

| Catalog Number | Height | Width | Thread Length | Torque  | Certifications |
|----------------|--------|-------|---------------|---------|----------------|
| 21101-749      | 8mm    | 8mm   | 12.3mm        | 0.3N·m  | RoHS           |
| 21100-268      |        |       |               | 0.22N·m |                |
| 21101-106      |        |       |               | 0.22N·m |                |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

