

# nVent LENTON Interlok Grommet



The nVent LENTON Grommet is used in conjunction with the nVent LENTON Bolted Form Mount and nVent LENTON Toggle Form Mount. These Grommets are used to secure nVent LENTON Interlok Grout-Fill Coupler variants in repeatable locations in the formwork. Once a Grout-Fill Coupler is placed over a Grommet, the Form Mount bolt is tightened, which expands the outside diameter of the Grommet, thus holding the Grout-Fill Coupler in place.

## FEATURES

Color-coded for the appropriate coupler size

Durable and reusable

**Material:** Polyester Urethane

## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Diameter 1 (Ø1) | Diameter 2 (Ø2) | Length (L) | For Use With      | Color  |
|----------------|----------------|-----------------|-----------------|------------|-------------------|--------|
| LK307A         | 145811         | 46 mm           | 19 mm           | 52mm       | LK5, LK6, LK7     | Blue   |
| LK308A         | 145812         | 49 mm           | 19 mm           | 52mm       | LK8               | Red    |
| LK320A         |                | 43 mm           | 19 mm           | 51mm       | LK20              | Yellow |
| LK316A         |                | 40 mm           | 19 mm           | 51mm       | LK16              | Black  |
| LK309A         | 145813         | 52 mm           | 19 mm           | 52mm       | LK9               | Black  |
| LK310A         | 145814         | 57 mm           | 19 mm           | 52mm       | LK10              | Yellow |
| LK311A         | 145815         | 60 mm           | 19 mm           | 52mm       | LK11              | Blue   |
| LK314A         | 145816         | 67 mm           | 19 mm           | 52mm       | LK12, LK40, LKT14 | Red    |
| LK318A         | 145817         | 83 mm           | 19 mm           | 52mm       | LKT18, LKT50      | Black  |

Table 2/2


| Catalog Number | Article Number | Unit Weight | Package Quantity |
|----------------|----------------|-------------|------------------|
| LK307A         | 145811         | 0.08 kg     |                  |
| LK308A         | 145812         | 0.09 kg     |                  |

| Catalog Number | Article Number | Unit Weight | Package Quantity |
|----------------|----------------|-------------|------------------|
| LK320A         |                | 0.15 kg     | 1                |
| LK316A         |                | 0.12 kg     | 1                |
| LK309A         | 145813         | 0.11 kg     |                  |
| LK310A         | 145814         | 0.13 kg     |                  |
| LK311A         | 145815         | 0.15 kg     |                  |
| LK314A         | 145816         | 0.22 kg     | 1                |
| LK318A         | 145817         | 0.5 kg      | 1                |

## ADDITIONAL PRODUCT DETAILS

Prior to installation, please read and understand the detailed instructions and safety notices provided in the nVent LENTON Interlok Instruction Manual.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**