

# Panhead Screw, Torx with Grounding



Good compromise between profile height and bearing area. Better load distribution than round heads.  
Compatible with automated assembly.

## FEATURES

For fixing Horizonrail rails or chassis plate and covers onto Side panel, with GND/ Earthing function

Torx imprint bears greater torque

The star-shaped head prevents cam-out

|                        |               |
|------------------------|---------------|
| <b>Finish:</b>         | Zinc Plated   |
| <b>Material:</b>       | Steel         |
| <b>Product Family:</b> | EuropacPRO    |
| <b>Product Type:</b>   | Screw         |
| <b>Type:</b>           | Panhead Screw |



## SPECIFICATIONS

| Catalog Number | Length | Package Quantity | Thread Size | Works With | Thread Length | Torque |
|----------------|--------|------------------|-------------|------------|---------------|--------|
| 24560-130      | 14mm   | 100              | M4          | Subracks   | 14mm          | 1.2N·m |
| 24560-131      | 14mm   | 10               | M4          | Subracks   | 14mm          | 1.2N·m |
| 24560-151      | 6mm    | 100              | M4          | Subracks   | 6mm           | 1.2N·m |
| 24560-155      | 10mm   | 100              | M4          | Subracks   | 10mm          | 1.2N·m |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

