

# nVent CADDY Pyramid PEK Wall Mount Support

The nVent CADDY Pyramid Wall Mount Equipment Support is a quick and easy solution for supporting HVAC mini-split units on a vertical surface. HVAC installers and mechanical contractors can utilize this cost-effective and simple yet innovative product on equipment installations. The nVent CADDY Pyramid Wall Mount Equipment Support is designed for outdoor use in demanding environments and features hot-dip galvanized construction and hardware.

## FEATURES

Visually appealing when hidden behind HVAC mini splits

High weight capacity for larger units and greater flexibility

Adjustable width to fit a range of equipment sizes and outputs

Straight-forward and simplified installation process

## SPECIFICATIONS

Table 1/3

| Catalog Number | Finish             | Material | Width (W) | A        | B        | Height (H) |
|----------------|--------------------|----------|-----------|----------|----------|------------|
| PEKWM          | Hot-Dip Galvanized | Steel    | 688.97 mm | 406.4 mm | 609.6 mm | 304.8 mm   |

Table 2/3

| Catalog Number | Hole Size (HS) | Length 1 (L1) | Length 2 (L2) | Length 3 (L3) | C                | Width 1 (W1)     |
|----------------|----------------|---------------|---------------|---------------|------------------|------------------|
| PEKWM          | 7.938 mm       | 127 mm        | 254 mm        | 717.6mm       | 190.5 - 444.5 mm | 482.6 - 968.4 mm |

Table 3/3

| Catalog Number | Width 2 (W2)   | Unit Weight | Ultimate Static Load (F) | Static Load Safety Factor |
|----------------|----------------|-------------|--------------------------|---------------------------|
| PEKWM          | 41.3 - 88.9 mm | 15 kg       | 2668N                    | 3:1                       |

WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE

