

Wire Basket Tray, Round Wire

The nVent CADDY Wire Basket Tray, Round Wire is a continuous pathway solution to support high-performance cabling systems while providing an ideal foundation for datacom and electrical contractors.

FEATURES

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fiber optic

UL Classified as an equipment ground conductor, no field removal of paint required

T-Weld edge wire for cable and installer protection

Mill Certificates are available to document recycled content for possible LEED credits/certification

Material: Steel

SPECIFICATIONS

Catalog Number	Finish	Color	Height (H)	Width (W)	Length (L)	Unit Weight
WBT2X4PW	Pregalvanized	Pewter	50 mm	100	3000mm	3.629 kg
WBT2X6PW	Pregalvanized	Pewter	50 mm	150	3000mm	4.082 kg
WBT2X12PW	Pregalvanized	Pewter	50 mm	300	3000mm	6.35 kg
WBT2X8PW	Pregalvanized	Pewter	50 mm	200	3000mm	4.436 kg
WBT2X24PW	Pregalvanized	Pewter	50 mm	600	3000mm	10.886 kg
WBT2X18PW	Pregalvanized	Pewter	50 mm	450	3000mm	8.618 kg
WBT4X12PW	Pregalvanized	Pewter	100 mm	300	3000mm	8.165 kg
WBT4X18PW	Pregalvanized	Pewter	100 mm	450	3000mm	10.433 kg
WBT4X24PW	Pregalvanized	Pewter	100 mm	600	3000mm	13.154 kg
WBT4X6PW	Pregalvanized	Pewter	100 mm	150	3000mm	4.99 kg
WBT4X4PW	Pregalvanized	Pewter	100 mm	100	3000mm	4.536 kg
WBT4X8PW	Pregalvanized	Pewter	100 mm	200	3000mm	6.35 kg
WBT6X18PW	Pregalvanized	Pewter	150 mm	450	3000mm	11.34 kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

