

CableTek Vertical Cable Manager

The CableTek Vertical Cable Manager's are available in single- and double-sided models. It mounts on the sides of or between 2- and 4-post open frame racks. The front side of the manager provides support, management and high capacity for patch cords, while the back supports Cat 5e, 6, 6A and fiber optic cables.

FEATURES

Easily removable one-piece front cover with access from right or left as needed opens 180° to allow full access to cables

Self-aligning bolt locations minimize lifting and speed installation

Self-captivating fasteners; bolt doesn't turn while tightening nut

Generous finger depth allows for maximum cable density and allows smooth transitions from vertical to horizontal positions

Unobstructed cable access to rack equipment - no keep-out areas

Rounded edges on composite material and grommets protect cable jackets from damage

Robust arrowhead fingers are shaped to funnel cables into base and are made of composite material

Cable tie-down points provided on back

Pass-through holes protect cable while facilitating routing between front and back

Single central door latch allows quick and easy access to cables

Double-sided cable manager with front and rear supporting fingers includes snap-on cover

Double-sided cable manager with posts and gates support and contain cables. Three sets of posts and gates are included; additional sets are available as accessories

Posts snap into pre-punched holes in the back of the cable manager

Gates snap onto posts, open from left or right as needed and swing 280° for cable access. Posts can be used alone as slack spools to control long patch cords.

Horizontal and vertical cable managers designed as a system for streamlined appearance and improved functionality

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
DV6DF7W	36096	Aluminum	Powder Coated	Signal White	RAL 9003	2mm
DV6D7 	17275	Aluminum	Powder Coated	Jet Black	RAL 9005	2mm
DV10D9	17293	Aluminum	Powder Coated	Jet Black	RAL 9005	2mm

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
DV6DF7 	26284	Aluminum	Powder Coated	Jet Black	RAL 9005	2mm
DV12D9	17295	Aluminum	Powder Coated	Jet Black	RAL 9005	2mm
DV6S7W	36093	Aluminum	Powder Coated	Signal White	RAL 9003	2mm
DV10DF7 	26285	Aluminum	Powder Coated	Jet Black	RAL 9005	2mm
DV12DF7W	36098	Aluminum	Powder Coated	Signal White	RAL 9003	2mm
DV10S7W	36094	Aluminum	Powder Coated	Signal White	RAL 9003	2mm
DV10S8	17284	Aluminum	Powder Coated	Jet Black	RAL 9005	2mm
DV12S8	17286	Aluminum	Powder Coated	Jet Black	RAL 9005	2mm
DV6S7 	17274	Aluminum	Powder Coated	Jet Black	RAL 9005	2mm
DV10DF7W	36097	Aluminum	Powder Coated	Signal White	RAL 9003	2mm
DV10S7	17276	Aluminum	Powder Coated	Jet Black	RAL 9005	2mm
DV12S9	17294	Aluminum	Powder Coated	Jet Black	RAL 9005	2mm
DV12DF7	26286	Aluminum	Powder Coated	Jet Black	RAL 9005	2mm
DV6DF8	26287	Aluminum	Powder Coated	Jet Black	RAL 9005	2mm
DV10DF8	26288	Aluminum	Powder Coated	Jet Black	RAL 9005	2mm
DV10S9	17292	Aluminum	Powder Coated	Jet Black	RAL 9005	2mm
DV12D8	17287	Aluminum	Powder Coated	Jet Black	RAL 9005	2mm

Table 2/2

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
DV6S9	17288	Aluminum	Powder Coated	Jet Black	RAL 9005	2mm
DV12S7W	36095	Aluminum	Powder Coated	Signal White	RAL 9003	2mm
DV6D8	17283	Aluminum	Powder Coated	Jet Black	RAL 9005	2mm
DV10D8	17285	Aluminum	Powder Coated	Jet Black	RAL 9005	2mm
DV6D9	17291	Aluminum	Powder Coated	Jet Black	RAL 9005	2mm
DV10D7 	17277	Aluminum	Powder Coated	Jet Black	RAL 9005	2mm
DV12D7	17281	Aluminum	Powder Coated	Jet Black	RAL 9005	2mm
DV12S7	17278	Aluminum	Powder Coated	Jet Black	RAL 9005	2mm
DV12DF8	26291	Aluminum	Powder Coated	Jet Black	RAL 9005	2mm
DV6S8	17282	Aluminum	Powder Coated	Jet Black	RAL 9005	2mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE