

Panels for Free-Stand Multi-door Enclosure with Mounting Stud

Use these panels in Free-stand Multi-Door Enclosures with Mounting Stud. Extra holes are provided for lifting and installing panels. Catalog numbers with BG suffix include two conductive panels bolted together with top and bottom stiffeners for additional support.

FEATURES

Panel mounting hardware is furnished with all enclosures which accept these panels

Material: Mild Steel

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Height	Width	Finish	Color	Thickness
A84PM78B	57041	1829mm	1828mm	Powder Coated	White	3.04mm
A72PM28G	15037	1524mm	552mm	Galvanized		3.04mm
A72PM40G	15041	1524mm	857mm	Galvanized		3.04mm
A84PM78G 	15047	1829mm	1828mm	Galvanized		3.04mm
A86PM75G	15036	1981mm	1778mm	Galvanized		3.04mm
A72PM66B	57054	1524mm	1524mm	Powder Coated	White	3.04mm
A72PM78	33970	1524mm	1828mm	Powder Coated	White	3.04mm
A72PM40	33920	1524mm	857mm	Powder Coated	White	3.04mm
A72PM34	33910	1524mm	704mm	Powder Coated	White	3.04mm
A86PM75B	57038	1981mm	1778mm	Powder Coated	White	3.04mm
A84PM40 	33930	1829mm	857mm	Powder Coated	White	3.04mm
A90PM78	33990	1981mm	1828mm	Powder Coated	White	3.04mm
A90PM78B	57042	1981mm	1828mm	Powder Coated	White	3.04mm
A72PM66G	15045	1524mm	1524mm	Galvanized		3.04mm
A86PM37G	15035	1981mm	863mm	Galvanized		3.04mm
A72PM78G	15046	1524mm	1828mm	Galvanized		3.04mm
A72PM34G	15038	1524mm	704mm	Galvanized		3.04mm

Catalog Number	Article Number	Height	Width	Finish	Color	Thickness
A72PM78B	57084	1524mm	1828mm	Powder Coated	White	3.04mm
A72PM54G	15044	1524mm	1219mm	Galvanized		3.04mm
A84PM40G	15042	1829mm	857mm	Galvanized		3.04mm

Table 2/2

Catalog Number	Article Number	Height	Width	Finish	Color	Thickness
A72PM66	33960	1524mm	1524mm	Powder Coated	White	3.04mm
A72PM28	33900	1524mm	552mm	Powder Coated	White	3.04mm
A86PM75BG	38137	1981mm	1778mm	Galvanized		3.04mm
A90PM78G	15048	1981mm	1828mm	Galvanized		3.04mm
A84PM78BG	38136	1829mm	1828mm	Galvanized		3.04mm
A90PM40G	15043	1981mm	857mm	Galvanized		3.04mm
A72PM54	33950	1524mm	1219mm	Powder Coated	White	3.04mm
A86PM37	29980	1981mm	863mm	Powder Coated	White	3.04mm
A84PM78 	33980	1829mm	1828mm	Powder Coated	White	3.04mm
A86PM75	29990	1981mm	1778mm	Powder Coated	White	3.04mm
A90PM40	33940	1981mm	857mm	Powder Coated	White	3.04mm
A90PM78BG	38138	1981mm	1828mm	Galvanized		3.04mm

ADDITIONAL PRODUCT DETAILS

Catalog numbers ending in B or BG represent the 2-piece panels, reference drawing configuration 2 in spec sheet. For all other catalog numbers, reference drawing configuration 1 in spec sheet.

Catalog numbers with B suffix include two painted panels bolted together, with top and bottom stiffeners for additional support.

Use combination of panels for 3-5 Door Free-Stand Enclosures.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE