

# Panels for Free-Stand with Mounting Channel One-Door



Panel for Free-Stand Single- and Dual-Access One-Door Enclosures with Mounting Channel. Panels can be positioned anywhere along horizontal mounting channels (see dimension drawing Sections B-B for limitations). Half-length panels can be located in the upper or lower portion of the enclosure.

## FEATURES

Available in Full-Length and Half-Length

Plated mounting hardware is provided

**Material:** Mild Steel

## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Height | Width | Finish        | Color | Thickness |
|----------------|----------------|--------|-------|---------------|-------|-----------|
| A90P24F2       | 23510          | 1013mm | 508mm | Powder Coated | White | 2.66mm    |
| A72P30F2G      | 15003          | 784mm  | 660mm | Galvanized    |       | 2.66mm    |
| A60P24F1       | 21260          | 1219mm | 508mm | Powder Coated | White | 2.66mm    |
| A72P24F1G      | 14998          | 1524mm | 508mm | Galvanized    |       | 2.66mm    |
| A60P24F2       | 21270          | 632mm  | 508mm | Powder Coated | White | 2.66mm    |
| A72P24F1       | 23320          | 1524mm | 508mm | Powder Coated | White | 2.66mm    |
| A90P36F1G      | 15006          | 1981mm | 812mm | Galvanized    |       | 2.66mm    |
| A72P36F1G      | 15004          | 1524mm | 812mm | Galvanized    |       | 2.66mm    |
| A72P24F2       | 23330          | 784mm  | 508mm | Powder Coated | White | 2.66mm    |
| A72P24F2G      | 15001          | 784mm  | 508mm | Galvanized    |       | 2.66mm    |
| A72P36F2G      | 15005          | 784mm  | 812mm | Galvanized    |       | 2.66mm    |
| A90P36F2G      | 15007          | 1013mm | 812mm | Galvanized    |       | 2.66mm    |

| Catalog Number                                                                             | Article Number | Height | Width | Finish        | Color | Thickness |
|--------------------------------------------------------------------------------------------|----------------|--------|-------|---------------|-------|-----------|
| A90P36F2                                                                                   | 23390          | 1013mm | 812mm | Powder Coated | White | 2.66mm    |
| A72P36F1  | 23360          | 1524mm | 812mm | Powder Coated | White | 2.66mm    |
| A90P24F1                                                                                   | 23480          | 1981mm | 508mm | Powder Coated | White | 2.66mm    |
| A90P24F2G                                                                                  | 15011          | 1013mm | 508mm | Galvanized    |       | 2.66mm    |
| A72P36F2                                                                                   | 23370          | 784mm  | 812mm | Powder Coated | White | 2.66mm    |
| A60P36F1G                                                                                  | 14996          | 1219mm | 812mm | Galvanized    |       | 2.66mm    |
| A60P36F2                                                                                   | 21290          | 632mm  | 812mm | Powder Coated | White | 2.66mm    |
| A60P36F2G                                                                                  | 14997          | 632mm  | 812mm | Galvanized    |       | 2.66mm    |

Table 2/2

| Catalog Number                                                                             | Article Number | Height | Width | Finish        | Color | Thickness |
|--------------------------------------------------------------------------------------------|----------------|--------|-------|---------------|-------|-----------|
| A60P36F1                                                                                   | 21280          | 1219mm | 812mm | Powder Coated | White | 2.66mm    |
| A90P24F1G                                                                                  | 15008          | 1981mm | 508mm | Galvanized    |       | 2.66mm    |
| A72P30F2                                                                                   | 23350          | 784mm  | 660mm | Powder Coated | White | 2.66mm    |
| A72P30F1                                                                                   | 23340          | 1524mm | 660mm | Powder Coated | White | 2.66mm    |
| A90P36F1  | 23380          | 1981mm | 812mm | Powder Coated | White | 2.66mm    |
| A60P24F1G                                                                                  | 14994          | 1219mm | 508mm | Galvanized    |       | 2.66mm    |
| A60P24F2G                                                                                  | 14995          | 632mm  | 508mm | Galvanized    |       | 2.66mm    |
| A72P30F1G                                                                                  | 15002          | 1524mm | 660mm | Galvanized    |       | 2.66mm    |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**