


Front Handle, Retrofitting for RatiopacPRO



With this front handle the flexible and robust RatiopacPRO/-AIR case, is simple to convert for easier handling.

FEATURES

For retrofitting of cases with cover strip and replace it by a front handle

Material: Aluminum
Product Type: Handle
Type: Static



SPECIFICATIONS

Catalog Number	Package Quantity	Handle Type	Color	Finish	Product Family	Works With
24571-301	2	Front Handle	Grey	Powder Coated	RatiopacPRO	Cases, RatiopacPRO
24571-302	2	Front Handle	Grey	Powder Coated	RatiopacPRO	Cases, RatiopacPRO
24571-303	2	Front Handle	Grey	Powder Coated	RatiopacPRO	Cases, RatiopacPRO
24571-304	2	Front Handle	Grey	Powder Coated	RatiopacPRO AIR	Cases, RatiopacPRO AIR
24571-305	2	Front Handle	Grey	Powder Coated	RatiopacPRO AIR	Cases
24571-306	2	Front Handle	Grey	Powder Coated	RatiopacPRO AIR	Cases
24571-993	2	Front Handle	Grey	Powder Coated	RatiopacPRO	Cases, RatiopacPRO

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.