

Window Door, ADC



Electrical components can be viewed while the door is closed, which keeps unauthorized personnel out and maintains the ingress protection.

FEATURES

Description: To replace the standard door, it provides a clear view of the components installed inside the enclosure. The lock(s) are interchangeable with all nVent HOFFMAN's standard lock(s).

Material: 1.2 mm mild steel / 1.5 mm for enclosures with a height or width of 500 mm or greater / 2 mm for enclosures with a height or width of 800 mm or greater and 4 mm clear safety glass.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 55, TYPE 12, 13, IK 07.

Pack quantity: 1 door.

Material: Mild Steel
Finish: Powder Coated
Color: Light Gray
Color Code: RAL 7035

SPECIFICATIONS

Catalog Number	Height	Width	Depth	Thickness	Latch Quantity	Window Size
ADC03025R5	300mm	250mm	15mm	1.2mm	1	159 x 93mm
ADC03030R5	300mm	300mm	15mm	1.2mm	1	159 x 143mm
ADC04030R5	400mm	300mm	15mm	1.2mm	1	259 x 143mm
ADC04040R5	400mm	400mm	15mm	1.2mm	1	259 x 243mm
ADC05030R5	500mm	300mm	15mm	1.5mm	1	359 x 143mm
ADC05040R5	500mm	400mm	15mm	1.5mm	1	359 x 243mm
ADC06040R5	600mm	400mm	15mm	1.5mm	2	459 x 243mm
ADC06050R5	600mm	500mm	15mm	1.5mm	2	459 x 343mm
ADC06060R5	600mm	600mm	15mm	1.5mm	2	459 x 443mm
ADC07050R5	700mm	500mm	15mm	1.5mm	2	559 x 343mm
ADC08060R5	800mm	600mm	15mm	2mm	2	659 x 443mm
ADC10060R5	1000mm	600mm	15mm	2mm	1	859 x 427mm

Catalog Number	Height	Width	Depth	Thickness	Latch Quantity	Window Size
ADC10080R5	1000mm	800mm	15mm	2mm	1	859 x 627mm
ADC12060R5	1200mm	600mm	15mm	2mm	1	1059 x 427mm
ADC12080R5	1200mm	800mm	15mm	2mm	1	1059 x 627mm

ADDITIONAL PRODUCT DETAILS

* 3 point espagnolette locking. Not suitable for AFS.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

