



|                 |                                                                                   | $\Delta R^2$ can be simplified | $\Delta R^2$ combination not recommended |
|-----------------|-----------------------------------------------------------------------------------|--------------------------------|------------------------------------------|
| Length $\neq L$ |  | -                              | +                                        |
|                 |  | +                              | +                                        |
| Area $\neq A$   |  | +                              | +                                        |
|                 |  | +                              | +                                        |
| Length $\neq L$ |  | +                              | +                                        |
|                 |  | +                              | +                                        |
| Horizontal wall |  | +                              | +                                        |
|                 |  | +                              | +                                        |
| Side panel      |  | +                              | +                                        |
|                 |  | +                              | +                                        |
| Horizontal wall |  | +                              | +                                        |
|                 |  | +                              | +                                        |
| Side panel      |  | +                              | +                                        |
|                 |  | +                              | +                                        |

**34566-263**

## FEATURES

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings



Net Weight: 0.2kg

## ADDITIONAL PRODUCT DETAILS

Without M4 thread to front, without printing and without notch for 19" bracket.

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

