


Side Panels, SPM



These side panels will ensure that the ingress protection is maintained, which means that the electrical components will operate without any disturbances and protect personnel from injuries.

FEATURES

Description: Easy one man assembly. Sealed by an extruded, one piece polyurethane gasket and mounted with 8 screws and new patented retainers. Can be replaced by the side door DNS.

Material: 1.5 mm steel plate.

Finish: RAL 7035 structured powder coating.

Protection: IP 55, TYPE 12, 13 in combination with MCS. IP66, TYPE 4, 12, 13 in combination with MCS-HP.

Pack quantity: 2 panels with mounting accessories.

Thickness: 1.5mm
Finish: Powder Coated
Color Code: RAL 7035

SPECIFICATIONS

Catalog Number	Article Number	Height	Width	Depth	Color	Product Family
SPM2008R5	SPM2008R5	2000mm	19mm	800mm	Light Gray	Free-Standing
SPM1806R5	SPM1806R5	1800mm	19mm	600mm	Light Gray	Free-Standing
SPM2210R5		2200mm	19mm	1000mm	Light Gray	
SPM1808R5	SPM1808R5	1800mm	19mm	800mm	Light Gray	Free-Standing
SPM2005R5	SPM2005R5	2000mm	19mm	500mm	Light Gray	Free-Standing
SPM2004R5	SPM2004R5	2000mm	19mm	400mm	Light Gray	Free-Standing
SPM1205R5		1200mm	19mm	500mm	Light Grey	Free-Standing
SPM2006R5	SPM2006R5	2000mm	19mm	600mm	Light Gray	Free-Standing
SPM1605R5	SPM1605R5	1600mm	19mm	500mm	Light Gray	Free-Standing
SPM1606R5	SPM1606R5	1600mm	19mm	600mm	Light Gray	Free-Standing
SPM1804R5	SPM1804R5	1800mm	19mm	400mm	Light Gray	Free-Standing
SPM2206R5	SPM2206R5	2200mm	19mm	600mm	Light Gray	Free-Standing
SPM1805R5	SPM1805R5	1800mm	19mm	500mm	Light Gray	Free-Standing

Catalog Number	Article Number	Height	Width	Depth	Color	Product Family
SPM1106R5		1100mm	19mm	600mm	Light Gray	Free-Standing
SPM1406R5	SPM1406R5	1400mm	19mm	600mm	Light Gray	Free-Standing
SPM2010R5		2000mm	19mm	1000mm	Light Gray	Free-Standing
SPM2208R5	SPM2208R5	2200mm	19mm	800mm	Light Gray	Free-Standing
SPM1405R5	SPM1405R5	1400mm	19mm	500mm	Light Gray	Free-Standing

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE