


EuropacPRO Cover Plate for Bolting to Side Panel



A cover plate is used for electromagnetic shielding or as mechanical protection. The cover can be screwed onto the side panel.

FEATURES

For variable positioning of horizontal rails e.g. for PCBs with standard formats

Perforation degree 58%

Suitable for use with all horizontal rails

Material:	Aluminum
Product Type:	Cover Plate
Product Family:	EuropacPRO
Finish:	Passivated
Type:	Perforated
Works With:	Subracks



SPECIFICATIONS

Catalog Number	Rack Width	Depth	Package Quantity	Package Unit	Torque
24560-066	42HP	295mm	2	Pair	2.1N·m
24560-078	84HP	175mm	2	Pair	2.1N·m
24560-064	42HP	175mm	2	Pair	2.1N·m
24560-073	63HP	295mm	2	Pair	2.1N·m
24560-079	84HP	235mm	2	Pair	2.1N·m
24560-080	84HP	295mm	2	Pair	2.1N·m
24560-063	84HP	275mm	2	Pair	
24560-065	42HP	235mm	2	Pair	2.1N·m
24560-072	63HP	235mm	2	Pair	2.1N·m

Catalog Number	Rack Width	Depth	Package Quantity	Package Unit	Torque
24560-081	84HP	355mm	2	Pair	2.1N·m
24560-082	84HP	415mm	2	Pair	2.1N·m
24560-071	63HP	175mm	2	Pair	2.1N·m
24560-083	84HP	475mm	2	Pair	2.1N·m
24560-061	42HP	275mm	2	Pair	
24579-090	42HP	277.75mm	2	Pair	2.1N·m
24579-092	84HP	277.75mm	2	Pair	2.1N·m
24560-062	63HP	275mm	2	Pair	

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE