


# EuropacPRO Perforated Rail for Connector



Perforated flat rail for connector mounting i.a.w. EN 60603-2 and DIN 41612, on VT horizontal rails.

## FEATURES

In conjunction with rear horizontal rails, VT

For Connector Mounting in accordance with EN 60603-2, DIN 41612

**Finish:** Passivated  
**Material:** Aluminum  
**Product Type:** Perforated Rail



## SPECIFICATIONS

| Catalog Number | Rack Width | Package Quantity | Length       | Product Family                                                    | Works With          | Certifications |
|----------------|------------|------------------|--------------|-------------------------------------------------------------------|---------------------|----------------|
| 20822-046      | 40HP       | 4                | 203.2m<br>m  | EuropacPRO                                                        | Sub racks           | RoHS           |
| 20822-047      | 60HP       | 4                | 304.8m<br>m  | EuropacPRO, RatiopacPRO, RatiopacPRO<br>AIR, CompacPRO, PropacPRO | Sub racks,<br>Cases | RoHS           |
| 20822-048      | 84HP       | 4                | 431.8m<br>m  | EuropacPRO, RatiopacPRO, RatiopacPRO<br>AIR, CompacPRO, PropacPRO | Sub racks,<br>Cases | RoHS           |
| 20822-049      | 28HP       | 4                | 142.24m<br>m | EuropacPRO, RatiopacPRO, RatiopacPRO<br>AIR, CompacPRO, PropacPRO | Sub racks,<br>Cases | RoHS           |
| 20822-050      | 42HP       | 4                | 213.36m<br>m | EuropacPRO, RatiopacPRO, RatiopacPRO<br>AIR, CompacPRO, PropacPRO | Sub racks,<br>Cases | RoHS           |
| 20822-051      | 20HP       | 4                | 101.6m<br>m  | EuropacPRO                                                        | Sub racks           | RoHS           |
| 20822-052      | 4HP        | 4                | 20.32m<br>m  | EuropacPRO, RatiopacPRO, RatiopacPRO<br>AIR, CompacPRO, PropacPRO | Sub racks,<br>Cases |                |
| 20822-053      | 8HP        | 4                | 40.64m<br>m  | EuropacPRO, RatiopacPRO, RatiopacPRO<br>AIR, CompacPRO, PropacPRO | Sub racks,<br>Cases |                |

ADDITIONAL PRODUCT DETAILS

A threaded insert is required to secure the perforated rail on the horizontal rail.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

