


# RatiopacPRO/-AIR Strap Handle



Strap handle for RatiopacPRO/-AIR with a static load-carrying capacity of 20 kg. Retrofittable without mechanical tooling on case.

### FEATURES

Static load-carrying capacity 20 kg

Retrofittable without mechanical tooling on the case side panel

**Product Family:** RatiopacPRO; RatiopacPRO AIR  
**Product Type:** Handle  
**Works With:** Cases



### SPECIFICATIONS

| Catalog Number | Rack Height | Depth | Package Quantity | Handle Type |
|----------------|-------------|-------|------------------|-------------|
| 24571-308      | 3U          | 315mm | 1                | Strap       |
| 24571-309      | 3U          | 375mm | 1                | Strap       |
| 24571-310      | 3U          | 435mm | 1                | Strap       |
| 24571-314      | 4U          | 315mm | 1                | Strap       |
| 24571-315      | 4U          | 375mm | 1                | Strap       |
| 24571-316      | 4U          | 435mm | 1                | Strap       |

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

## North America

All locations

+1.763.422.2661

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

## Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

## Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

## Middle East & India

Dubai, United Arab  
Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.