

# Mounting Plates Power Distribution, BMP



The steel mounting plate contributes to speeding up the assembly of the terminal box since it can be machined easily and equipped with components before being mounted.

## FEATURES

Description: Steel mounting plate for terminal boxes.

Material: 2 mm galvanized steel.

Pack quantity: 1 piece.

**Material:** Mild Steel  
**Finish:** Galvanized  
**Thickness:** 2mm

## SPECIFICATIONS

| Catalog Number | Height | Width | Depth | Panel Size  | Enclosure Material |
|----------------|--------|-------|-------|-------------|--------------------|
| BMP1515        | 150mm  | 150mm | 2mm   | 125 x 120mm | Mild Steel         |
| BMP1530        | 150mm  | 300mm | 2mm   | 125 x 270mm | Mild Steel         |
| BMP2020        | 200mm  | 200mm | 2mm   | 175 x 170mm | Mild Steel         |
| BMP2030        | 200mm  | 300mm | 2mm   | 175 x 270mm | Mild Steel         |
| BMP2040        | 200mm  | 400mm | 2mm   | 175 x 370mm | Mild Steel         |
| BMP2050        | 200mm  | 500mm | 2mm   | 175 x 470mm | Mild Steel         |
| BMP2060        | 200mm  | 600mm | 2mm   | 180 x 570mm | Mild Steel         |
| BMP2080        | 200mm  | 800mm | 2mm   | 180 x 770mm | Mild Steel         |
| BMP3030        | 300mm  | 300mm | 2mm   | 275 x 270mm | Mild Steel         |
| BMP3040        | 300mm  | 400mm | 2mm   | 275 x 370mm | Mild Steel         |
| BMP3050        | 300mm  | 500mm | 2mm   | 275 x 470mm | Mild Steel         |
| BMP3060        | 300mm  | 600mm | 2mm   | 280 x 570mm | Mild Steel         |
| BMP4040        | 400mm  | 400mm | 2mm   | 375 x 370mm | Mild Steel         |

| Catalog Number | Height | Width | Depth | Panel Size  | Enclosure Material |
|----------------|--------|-------|-------|-------------|--------------------|
| BMP4060        | 400mm  | 600mm | 2mm   | 380 x 570mm | Mild Steel         |
| BMP4080        | 400mm  | 800mm | 2mm   | 380 x 770mm | Mild Steel         |

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

