

# Locking System For Lift Handles, LHC

The locking inserts and cylinders can be mounted independently in the lift handle, which means many combinations can be created. This reduces the number of handles to be stocked.



## FEATURES

Description: Profile half cylinder locks. Designed to be used with LLH/LLHS handles.

Pack quantity: 1 piece.

**Finish:** Smooth Matte

**Color:** Black Gray

## SPECIFICATIONS

| Catalog Number | Article Number | Height | Width | Depth | Key Type                                            | Key Code |
|----------------|----------------|--------|-------|-------|-----------------------------------------------------|----------|
| LHC521         | LHC521         | 37mm   | 23mm  | 41mm  | Ronis                                               | C21323   |
| LHC5212132E    | LHC5212132E    | 37mm   | 23mm  | 41mm  | Ronis                                               | 2132E    |
| LHC5213121E    | LHC5213121E    | 37mm   | 23mm  | 41mm  | Ronis                                               | 3121E    |
| LHC522         | LHC522         | 37mm   | 23mm  | 41mm  | Ronis                                               | C21323   |
| LHC523         | LHC523         | 37mm   | 23mm  | 41mm  | Square 7 mm                                         |          |
| LHC524         | LHC524         | 37mm   | 23mm  | 41mm  | Square 8 mm                                         |          |
| LHC526         | LHC526         | 37mm   | 23mm  | 41mm  | Triangle 7 mm                                       |          |
| LHC527         | LHC527         | 37mm   | 23mm  | 41mm  | Triangle 8 mm                                       |          |
| LHC528         | LHC528         | 37mm   | 23mm  | 41mm  | Double-bit 3 mm                                     |          |
| LHC529         | LHC529         | 37mm   | 23mm  | 41mm  | Double-bit 5 mm                                     |          |
| LHC530         | LHC530         | 37mm   | 23mm  | 41mm  | Daimler Benz                                        |          |
| LHC531         | LHC531         | 37mm   | 23mm  | 41mm  | Lock insert slotted 2x4 mm                          |          |
| LHC533         | LHC533         | 37mm   | 23mm  | 41mm  | Cylinder N°E1 (VW), key excluded                    |          |
| LHC534         | LHC534         | 37mm   | 23mm  | 41mm  | Adapter for other profile half cylinders (DIN18252) |          |
| LHC535         | LHC535         | 37mm   | 23mm  | 41mm  | Adapter for ASSA ABLOY and Trio Ving cylinders      |          |
| LHC536         | LHC536         | 37mm   | 23mm  | 41mm  | Push button only                                    |          |

## ADDITIONAL PRODUCT DETAILS

---

\* Other key numbers available on request. \*\* Key numbers 333, 1333, EK333 and GX130 are equal. \*\*\* Order separate key LSMK for Square 8 mm and Triangle 8 mm.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.