

# Door Mounting Profiles, MMDP



These mounting profiles will ensure that the enclosure's door does not bend and allows electrical components and other accessories to be fitted easily.

## FEATURES

**Description:** To strengthen the door and provide further mounting possibilities. Mounted on the inside of the door onto M6 welded studs. Equipped with a 10 mm hole pattern. These door profiles cannot be used with the AFS enclosure range.

**Material:** 1.2 mm galvanized steel.

**Dimension:** 15 x 14 mm.

**Pack quantity:** 1 pair with mounting accessories.

**Thickness:** 1.2mm  
**Finish:** Galvanized  
**Material:** Mild Steel

## SPECIFICATIONS

| Catalog Number | Article Number | Height | Width | Depth | Product Family                        | Enclosure Material |
|----------------|----------------|--------|-------|-------|---------------------------------------|--------------------|
| MMDP050        | MMDP050        | 438mm  | 15mm  | 14mm  | Wall Mounted, Human Machine Interface | Mild Steel         |
| MMDP120        | MMDP120        | 1138mm | 15mm  | 14mm  | Wall Mounted, Human Machine Interface | Mild Steel         |
| MMDP040        | MMDP040        | 338mm  | 15mm  | 14mm  | Wall Mounted, Human Machine Interface | Mild Steel         |
| MMDP140        | MMDP140        | 1338mm | 15mm  | 14mm  | Wall Mounted, Human Machine Interface | Mild Steel         |
| MMDP060        | MMDP060        | 538mm  | 15mm  | 14mm  | Wall Mounted, Human Machine Interface | Mild Steel         |
| MMDP070        | MMDP070        | 638mm  | 15mm  | 14mm  | Wall Mounted, Human Machine Interface | Mild Steel         |
| MMDP080        | MMDP080        | 738mm  | 15mm  | 14mm  | Wall Mounted, Human Machine Interface | Mild Steel         |
| MMDP100        | MMDP100        | 938mm  | 15mm  | 14mm  | Wall Mounted, Human Machine Interface | Mild Steel         |

## ADDITIONAL PRODUCT DETAILS

Not suitable for AFS.

## **WARNING**

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**