

Stainless Steel Plain Door, DNSS



This door replaces the rear panel in a floor standing enclosure to allow for rear access of equipment installed in the front, or for using back to back mounting plates to increase the enclosure's mounting space.

FEATURES

Description: Standard door equipped with double-bit 3 mm lock system and door frame. Door accessory kit DNMKs (hinges, rod catches) to be ordered separately. Allows all the options of the locking programme and 180° hinges. Compatible with combinable and compact stainless steel enclosure ranges.

Material: 2 mm AISI 304 stainless steel plate / AISI 316L (on request).

Maximum load: 800 N.

Finish: 400 pre-grained stainless steel.

Pack quantity: 1 piece.

Mounting requirements: Use hinge kit DNMKs if no door was fitted previously.

Material: Stainless Steel 304
Finish: Brushed
Thickness: 2mm

SPECIFICATIONS

Table 1/2

Catalog Number	E-Number	Height	Width	Depth	Door Type	Product Family
DNSS1212L	2411251	1200mm	600mm	17mm	Left Door	Free-Standing
DNSS1212R	2411252	1200mm	600mm	17mm	Right Door	Free-Standing

Catalog Number	E-Number	Height	Width	Depth	Door Type	Product Family
DNSS1408	2411253	1400mm	800mm	17mm	Single Door	Free-Standing
DNSS1606	2411254	1600mm	600mm	17mm	Single Door	Free-Standing
DNSS1608	2411255	1600mm	800mm	17mm	Single Door	Free-Standing
DNSS1610	2411256	1600mm	1000mm	17mm	Single Door	Free-Standing
DNSS1612L	2411257	1600mm	600mm	17mm	Left Door	Free-Standing
DNSS1612R	2411258	1600mm	600mm	17mm	Right Door	Free-Standing
DNSS1806	2411259	1800mm	600mm	17mm	Single Door	Free-Standing
DNSS1808	2411260	1800mm	800mm	17mm	Single Door	Free-Standing
DNSS1810	2411261	1800mm	1000mm	17mm	Single Door	Free-Standing
DNSS1810L	2411262	1800mm	500mm	17mm	Left Door	Free-Standing
DNSS1810R	2411263	1800mm	500mm	17mm	Right Door	Free-Standing
DNSS1812L	2411264	1800mm	600mm	17mm	Left Door	Free-Standing
DNSS1812R	2411265	1800mm	600mm	17mm	Right Door	Free-Standing
DNSS1816L	2411266	1800mm	800mm	17mm	Left Door	Free-Standing
DNSS1816R	2411267	1800mm	800mm	17mm	Right Door	Free-Standing
DNSS2006	2411268	2000mm	600mm	17mm	Single Door	Free-Standing
DNSS2008	2411269	2000mm	800mm	17mm	Single Door	Free-Standing
DNSS2010	2411272	2000mm	1000mm	17mm	Single Door	Free-Standing

Table 2/2

Catalog Number	E-Number	Height	Width	Depth	Door Type	Product Family
DNSS2012L	2411275	2000mm	600mm	17mm	Left Door	Free-Standing
DNSS2012R	2411276	2000mm	600mm	17mm	Right Door	Free-Standing
DNSS2016L	2411277	2000mm	800mm	17mm	Left Door	Free-Standing
DNSS2016R	2411278	2000mm	800mm	17mm	Right Door	Free-Standing

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

