


Panhead Screw, Torx



Good compromise between profile height and bearing area. Better load distribution than round heads.
Compatible with automated assembly.

FEATURES

- Torx imprint bears greater torque
- The star-shaped head prevents cam-out

Material: Steel
Product Type: Screw
Type: Panhead Screw



SPECIFICATIONS

Table 1/2						
Catalog Number	Length	Finish	Package Quantity	Thread Size	Product Family	Works With
24560-148	10mm	Nickel Plated	100	M2.5		Backplanes, Test Adapters
24560-147	7mm	Nickel Plated	100	M2.5	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO	Front Panels, Eurorack, Novastar, Varistar, Varistar CP
24560-135	6mm	Zinc Plated	100	M4	EuropacPRO	Subracks
24560-161	12mm	Nickel Plated	100	M2.5		Backplanes, Test Adapters
24560-162	14mm	Nickel Plated	100	M2.5		Backplanes, Test Adapters
24560-163	16mm	Nickel Plated	100	M2.5		Backplanes, Test Adapters
24560-178	6mm	Nickel Plated	100	M2.5	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO	Front Panels, Eurorack, Novastar, Varistar, Varistar CP

Table 2/2

Catalog Number	Thread Length	Torque
24560-148	10mm	0.3N·m
24560-147	7mm	0.3N·m
24560-135	6mm	1.2N·m
24560-161	12mm	0.3N·m
24560-162	14mm	0.3N·m
24560-163	16mm	0.3N·m
24560-178	6mm	0.3N·m

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

